



Synergy Global Technology Inc


www.RackmountMart.com

Basic Rack PDU

Overview

Outlets. The Rack PDU has twenty (20) IEC-320-C13 outlets, and four (4) IEC-320-C19 outlets.

Power cord. The 3-foot (0.91-meter) power cord terminates with a IEC-309 16 A connector.



RA5024-C-16A-IEC

Specifications

Electrical

Input connector	IEC-309 16 A plug
Output connectors	(20) IEC-320-C13, (4) IEC-320-C19 outlets
Nominal input voltage	230 VAC
Acceptable input voltage	± 10% of normal voltage
Input frequency	47–63 Hz
Cord length	0.91 m (3 ft)

Physical

(H × W × D)	161.92×5.56×4.39 cm (63.75×2.19×1.73 in)
Shipping dimensions (H × W × D)	213.36×15.24×12.7 cm (84.00×6.00×5.00 in)
Weight	5.56 kg (12.25 lb)

Environmental

Maximum elevation (above MSL)	
Operating	15 000 ft (4500 m)
Storage	50 000 ft (15 000 m)
Temperature	
Operating	–5 to 45° C (23 to 115° F)
Storage	–25 to 65° C (–13 to 149° F)
Humidity	
Operating	5–95% RH non-condensing
Storage	5–95% RH non-condensing

Compliance

Safety verification	VDE 0805, CE, EN 60950, IEC 60950
---------------------	--------------------------------------



Synergy Global Technology Inc

www.RackmountMart.com