

CR4824 19" 800mm Depth 24U Rack Cabinet



Features:

- 24u rack cabinet
- Compatible with ANSI/EIA RS-310-D, IEC297-2, DIN41494, DIN41494, ETSI standard
- 23.62(W) x 31.5(D) x 49(H) inch
- 71% ventilated rate of the high-density vented door
- Heavy duty casters and leveling feet
- Removable side panels
- Designed for enhanced airflow
- Four post, depth-adjustable rack system with 19" mounts and square holes
- Perforated roof with cable entry access in the rear
- Perforated front and rear locking doors (easily removable)

Specifications:

- ▶ Capacity: 24u
- ▶ Dimension: 23.62(W) x 31.5(D) x 49(H) inch
- ▶ Material: SPCC cold rolled steel
- ▶ Thickness: mounting profile 2.0mm, mounting angle 1.5mm, others 1.2mm
- ▶ Surface finish: Degreasing, pickling, phosphoric, powder coated
- ▶ Degree of protection: IP20
- ▶ Loading capacity: 1670 lbs
- ▶ Main parts: top cover 1pcs, mounting profile 4pcs, mounting angle 6pcs, spring lock 2pcs, key 4pcs, vented front door 1pcs, heavy duty caster 4pcs, frame 2pcs, side panel 2pcs, bottom panel 1pcs, M6 B-head screw 40pcs, M6 square nut 40pcs, Allen wrench 1pcs, M12 adjustable feet 4pcs