

LCDR8U22-05 8U Rackmount 21.5" WIDE LCD RACK MONITOR (FULL HD)



Made in U.S.A.

- Mounts in 8U of rack space with mounting brackets to fit 19" rack width.
- 21.5" Wide format TFT LCD display with full HD 1920 x 1080 resolution.
- Fast video response time provides sharp text and crisp motion.
- 16:9 aspect ratio provides a widescreen viewing area.
- 15,000:1 Dynamic contrast ratio for superior detail.



LCDR8U22-05 shown mounted in a standard 19" equipment rack.

GENERAL SPECIFICATIONS

Dimensions:

22.0" (W) x 14.0" (H) x 2.8" (D)

Weight:

16.5 lbs.

Power:

100 - 240 VAC, 50/60 Hz.

45 Watts max.

Plug & Play:

DDC2B

Temperature:

Operating: 10°C to 40°C

Storage: -20°C to 45°C

Humidity:

Operating: 10 to 80% RH (max)

Input Video Signals:

R.G.B. analog, DVI (with HDCP)

Sync Type:

Separate H/V, Composite H/V, SOG.

Input Connectors:

15 pin D-sub, DVI-D.

Compatibility:

PC/Windows, Macintosh.

Colors Available:

Black.

DISPLAY SPECIFICATIONS

Display Type:

a-si TFT/TN

Viewable Size:

21.5" wide format.

Colors Displayed:

16.7 million colors.

Contrast Ratio (Typ/Dyn):

1000:1 / 15000:1

Brightness:

300 cd/m² typ.

Viewing Angle (CR>5):

Horizontal: 170°

Vertical: 160°

Response Time:

5 ms (G to G)

Native Resolution:

1920 x 1080

(16:9 Format)

Specifications subject to change without notice.

MODEL NUMBER

LCDR8U22-05 (add 'L' for Lexan™ screen protection option)

*Contact us about other options and
our additional rack mount products.*