

ID-32Pw-LED 32" Widescreen LCD Display

Universal open frame mounting




Display Benefits

- ▶ 32" widescreen LCD supports Full HD 1080p resolution
- ▶ PIP & Picture by Picture viewing efficiency
- ▶ Green LED-backlit panel technology
- ▶ Rugged construction against external impact
- ▶ Standard with HDMI, DVI-D, VGA, S-Video, RCA, Audio & remote controller

Options

- 3G / HD / SD-SDI Broadcast-grade input
- MC Multi-display control solution
- Projected Capacitive (10-point touch)
Capacitive (single point touch)
- MIL-type or lockable connector
- 48V, 24V or 12VDC power
- TV - Analog

Basic I/O



Specifications

LCD Panel

Manufacturer :	 LG
Size (diagonal) :	32" Widescreen TFT
Max resolution :	1920 x 1080
Brightness (cd/m2) :	360
Backlight :	LED
Colors :	16.7 M
Contrast ratio (typ) :	1400 : 1
Viewing angle (H/V) :	178° x 178°
Active area (mm) :	698 x 393
MTBF (hrs) :	50,000
Signal input :	HDMI / DVI-D / VGA / S-Video / RCA

Weight

Net : 16.4 kgs (36.1 lbs)

Mounting :

Universal mount / VESA mount

Environmental

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration (11 ms duration)
Vibration :	5~500Hz 1G RMS random vibration

Casing Color :

Black (RAL 9005)

Regulatory

Safety :	FCC & CE certified
Environmental :	RoHS2 & REACH compliant

Power

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 200 Watt, Standby 20 Watt

Dimensions

Product : 799 x 77 x 493 mm / 31.5 x 3 x 19.4 inch

Diagrams (mm)

