

# RM8006 8U 19" Rackmount Chassis



## Specifications

- EIA RS-310C 19" Rackmount Standard
- Construction: Heavy Duty Cold Rolled Electroplated Steel
- Color: Black (Standard), Beige or Custom
- System Boards: Dual Xeon, Pentium 4, AMD 64, Dual Opteron, Quad Opteron
- Support EATX M/B (Max. to 13" x 16") SSI EEB 3.0 With Removable Drawer
- Support 20-slot Passive Backplane With Removable Drawer
- Drive Capacity: 7x 5.25" & 1x 3.5"
- Power Supply (Optional): PS/2 Size Single up to 700W or Vertical Redundant up to 550W or Mini Redundant up to 500W ATX P/S (Rear Installation)
- Cooling: Hot Swappable 4x(90mm = 51CFM ea.) Fans & 1x (120mm = 108CFM ea.) Fan With Removable Air Filter
- Front Door: Single Door With Keylock
- Air Filter: Inside Front Door (Washable)
- Thermal Management Card: Installed
- Indicators: LEDs for Power ON/OFF, HDD Active, Fan, Temperature
- Flexible Hold Down Bar Designed
- Switch: Power ON/OFF Momentary (Pushbutton), System Reset, Buzzer Reset
- Dimensions (W x H x D): 483 x 356 x 510mm (19" x 16.5" x 18.2")
- Cuft: 7.4
- GW: 30.5 kgs / 67.3 lbs
- Humidity: 5% - 95% Non-condensing

## Dimension

