



- 17.3" Full HD (1920 x 1080 resolution) TFT LCD display
- Mounts flush in 6U (10.5") of vertical 19" rack space
- Steel front panel construction with a durable powder coat finish
- 600:1 Static contrast ratio provides superior detail
- HDMI, DP, and VGA inputs

GENERAL SPECIFICATIONS

Dimensions:

19.0" (W) x 10.5" (H) x 1.6" (D)

Weight:

7.5 lbs

Power:

110 - 240 VAC, 50/60 Hz
17 Watts typical

Temperature:

Operating: 0°C to 70°C
Storage: -20°C to 70°C

Humidity:

Operating: 5 to 95% RH (max)

Input Signal (VGA):

RGB analog video

Input Signal (Digital):

HDMI, DisplayPort (DP)

Input Connectors:

Analog: 15-pin mini D-Sub
Digital: HDMI, DP

Colors Available:

Black

DISPLAY SPECIFICATIONS

Display Type:

TFT active matrix LCD

Viewable Size:

17.0" diagonal

Colors Displayed:

16.7 million colors

Contrast Ratio :

600:1

Brightness:

400 cd/m² typ

Viewing Angles:

160°/140° H/V

Response Time:

37/3 ms Typ (Tr/Td)

Optimum Resolution

1920 x 1080

Light Source:

Long Life (50,000 hrs typ)

Panel Surface:

Anti-glare

Specifications subject to change without notice.



Offering OEM and custom solutions.
Contact us for additional information.