



Features

- Compact 19 inch rack mountable with 7U height
- 17.3 inch TFT LCD wide screen support 4K resolution 3840 x 2160
- Support 1920 x 1080 & 1920 x 1200 resolution
- Display-Port 1.4 x1 , HDMI 2.0 x 2
- 90 ° tilt adjustment while mounted in rack: 45° ~-45° (V)
- Heavy duty steel chassis with hardness glass protect screen
- Front osd control buttons to optimized display
- Build in 2x 2watts stereo speakers

Option

- DC 9~36 V power input
- AR Hardness glass
- Touch screen

LCD Characteristics :

Screen Size	17.3"
Backlight Type	LED
Resolution	3840x2160
Contrast Ratio	1000:1
Brightness (cd/m2)	400
View Angles (H/V)	178/178
Pixel Size (HxV) mm	0.0995x0.0995
Max. Color	16.7M
MTBF (Hrs.)	30,000

Input Signals:

Display-Port	Display- Port 1.4 (4K-60Hz)
HDMI	2 x HDMI 2.0 (4K-60Hz)
Power Input	AC inlet, 100-240VAC
Touch-USB (option)	USB A Type connector
Touch-RS232 (option)	D-SUB 9P connector (Female)

Power Specifications :

AC Power Input	Standard IEC Type Power Cord with Internal Power adapter, 100-240V AC Input
Wide Range DC Power Input (option)	Screw Type Terminal Block with internal wide Range DC 9-36V power module

User Controls Interface:

Power ON / OFF via Front Button
Power Mode Status LED indicator
OSD (On Screen Display) Buttons

Mechanical and Environment:

Height	7U
IP Protect	N/A
Mounting	VESA Mount and Rack Mount
Construction	Metal Housing
Operating Temperature	0 - 50 deg. C
Operating Humidity	5% - 95% (non -condensing)
Anti-Vibration	5 - 500 Hz / 1 Grms PTP
Anti-Shock	15G / Peak (11 ms)
Physical Dimension (WxHxD)	482 x 310 x 62 (mm)
Net Weight	7 (KGs)
Certification and Approvals	CE / FCC / RoHS

