

2U RACK MOUNT SPEAKER SYSTEM



Featuring a rugged fully enclosed amplified stereo speaker system with front panel controls which include a Power ON/OFF Switch and Indicator and a separate Volume Control. A Headphone Jack located on the front panel disables the internal speakers when a headphone plug is inserted, directing audio output to the headphones. The unit is supplied with a detachable audio cable and an external 110/220 VAC power supply. The rack mount ears are removable allowing the speaker to be mounted in other applications.

GENERAL SPECIFICATIONS

Dimensions:

19.0" (W) x 3.50" (H) x 4.0" (D)

Weight:

10 lbs

Power Supply:

12VDC out, 110/220 VAC, 50/60 Hz Input.
60 Watts maximum.

Colors Available:

Light Gray and Black (B).

Front Panel Controls:

Power ON/OFF switch, Volume control,
Headphone Jack, Power Indicator.

Audio Output:

24 Watts.

Audio Input Connector:

3.5mm stereo jack.

Specifications subject to change without notice.

Part # : RK1003



Contact us about other options and our additional rack mount products.