

1U Rack KVM Drawer 24" Depth | 19" SXGA, HB-SXGA, 17" FHD, HB-FHD & UHD

This configurable 1U clamshell KVM console combines a rugged aluminum enclosure with an integrated LCD display, keyboard and pointing device. Designed for standard 19-inch racks and transit cases, its 24-inch chassis accommodates diverse control and connectivity requirements.



Features

- 1U, 19-inch rackmount clamshell drawer; 24-inch depth
- Rugged aluminum construction; MIL-STD-810F/G design
- 17.3-inch or 19-inch LED-backlit LCD options
- Integrated keyboard and pointing device selections
- HDMI, DP, DVI, RJ45 (CAT6) and VGA KVM switches
- MIL-grade C300 friction slides and cable management
- Telescoping rear arms for rack or transit-case mounting

KVM Switch Options: HDMI KVM, DP KVM, DVI KVM, RJ45 KVM (CAT6 KVM), VGA KVM

Configuration Options

- High-brightness and optically bonded displays
- Resistive or PCAP touch interfaces
- CAC reader on compatible keyboards
- Controller and KVM switch selections
- Front-panel handles and locking latches
- 12V / 24V / 125V DC power options
- Selectable power inlet connectors




Available Display, Keyboard & KVM Configurations

KVM Switch Options



SD1: 4-port DisplayPort KVM switch



SE2u: 8-port VGA KVM switch



SG2x: 4-port DVI KVM switch



SO8: 8-port HDMI KVM switch



SIPx: 8 / 16 / 32-port RJ45 KVM switch

LCD Display Options

Model Number LCD1U19-34

19-inch SXGA | 1280 x 1024
350 nits | 1000:1 | 10 ms
Operating: -30°C to +85°C

Model Number LCD1U19-35

19-inch SXGA | 1280 x 1024
1600 nits | 1000:1 | 10 ms
Operating: -30°C to +70°C

Model Number LCD1U17-62

17.3-inch FHD | 1920 x 1080
400 nits | 600:1 | 40 ms
Operating: 0°C to +70°C

Model Number LCD1U17-63

17.3-inch FHD | 1920 x 1080
1000 nits | 600:1 | 40 ms
Operating: 0°C to +70°C

Model Number LCD1U17-64

17.3-inch UHD | 3840 x 2160
400 nits | 1000:1 | 27 ms
Operating: 0°C to +50°C

Keyboard Options



SQx: 97-key NEMA 4; touchpad
USB / PS2; 10M cycles



SA2x: 89-key; optical trackball
Cherry ML; 20M cycles



SI2u: 82-key; glide pad
Rubber membrane; 5M cycles



SHx: 113-key NEMA 4X; 3-button pointer
Silicone rubber; 10M cycles



SMx: 119-key; 3-button touchpad
Tactile ML; 50M operations

Configurations vary by display, input interface and application. Contact Rackmount Mart for availability.
LCD specifications shown are representative of the original manufacturer data; options may vary.