

Benefits

- ▶ 1U 18" LCD console drawer
- ▶ 1920 x 1200 **WUXGA** native resolution / 16.7M colors
- ▶ HDMI + VGA video input (speakers excluded)
- ▶ 104-key USB keyboard with either touchpad or trackball
- ▶ Short depth design of 470mm
- ▶ One Man installation design
- ▶ New enhanced aesthetics with molded front panel & 2-pt lock
- ▶ TAA Compliant

Options

- Dual stereo speakers for HDMI
- DP 1.0 + Speakers
- DVI-D + Audio input & output + Speakers
- 3G / HD / SD-SDI Broadcast-grade input (
- Front USB hub port for device access (
- DC power : 12V / 24V / 48V / 125V / 250V

Product Specifications

Console Port	
Video input	VGA + HDMI 1.4
KB / MS	USB interface
VGA console 6ft cable or HDMI console 6ft cable	Drawer end : DB-15 + USB type A x 2 Server end : DB-15 + USB type A x 2 Drawer end : HDMI + USB type A x 2 Server end : HDMI + USB type A x 2

LED-backlit LCD Panel	
Panel size (diagonal)	18"
Native resolution	1920 x 1200
Brightness (cd/m ²)	300
Contrast ratio (typ.)	1000 : 1
Colors	16.7 M
Viewing angle (L/R/U/D)	89/89/89/89
Response time (ms)	9
Dot pitch (mm)	0.202
Display area (mm)	387.76H x 242.35V
Surface treatment	Anti-glare
Surface hardness	3H
MTBF (hrs)	15,000

Physical		
Product (W x D x H)	Single console	442 x 470 x 44 mm 17.4 x 18.5 x 1.73 inch
	Console w/ KVM	442 x 590 x 44 mm 17.4 x 23.2 x 1.73 inch
Packing (W x D x H)	Single console /	590 x 808 x 140 mm
	Console w/ KVM	23.2 x 31.8 x 5.5 inch
Net weight	Single console	12 kg / 26.4 lb
	Console w/ KVM	13 kg / 28.6 lb
Gross weight	Single console	16.6 kg / 36.5 lb
	Console w/ KVM	19 kg / 41.8 lb

* All dimensions stated are subject to change if options are selected / integrated to base model part codes

Mounting Distance	
Single console drawer	470 ~ 700 mm 18.3 ~ 27.6 inch
Console w/ KVM drawer	470 ~ 800 mm 18.5 ~ 31.5 inch

Video Option		
Digital	DVI-D	DVI-D single link
	DisplayPort	DP 1.0 / HDCP 1.3

Audio Option		
Input	Connector	3.5mm stereo jack
	Impedance / Power level	30kΩ / 750mV
Output	Connector	3.5mm stereo jack
	Resistance / Power level	30kΩ / 2.8V
Speaker	Dual stereo	2W x 2

Power		
Input	Auto-sensing 100 to 240VAC, 50 / 60Hz	
Consumption (console / KVM)	Screen on	Max. 23W / Max. 48W
	Power saving mode	Max. 2W / Max. 34W
	Power button off	Max. 1W / Nil

Environment	
Operating temp.	0 to 55°C degree
Storage temp.	-20 to 60°C degree
Operating humidity	10~90%, non-condensing
Storage humidity	5 ~90%, non-condensing
Operating altitude	16,000 ft
Non-operating altitude	40,000 ft
Shock	10G acceleration (11ms duration)
Vibration	10~300Hz 0.5G RMS random vibration

Compliance	
EMC	FCC & CE
Safety	CE / LVD & UKCA
Environment	REACH & RoHS3 / WEEE

HDMI KVM	IP	Remote	8-port
	0	0	-8HD

HDMI USB KVM Cable		
		
LCD-A3008 (6ft) 4K HDMI - HDMI cable	LCD-A3009 (6ft) 4K HDMI - DP cable	LCD-A3011 (6ft) 2K HDMI - DVI-D cable

DP KVM	IP	Remote	8-port
	0	0	-8DP

DP USB KVM Cable	
Resolution	16:10 - max. 1920 x 1200
Support ** :	16:9 - max. 3840 x 2160
	LCD-A3013 (6ft) 4K DP - DP cable

DVI-D KVM	IP	Remote	12-port
	0	0	-12DVI

DVI-D USB KVM Cable	
Resolution	16:10 - max. 1920 x 1200
Support ** :	16:9 - max. 1920 x 1080
	4:3 - max. 1600 x 1200
	LCD-A3005 (6ft) LCD-A3006 (15ft)

Cat6 Matrix KVM	IP	Remote	8-port	16-port	32-port
	1	1	-	-MU163IP	-MU323IP
	2	1	-	-MU164IP2	-MU324IP2
	0	1	-	-MU162	-MU322
	0	2	-	-MU163	-MU323
	0	3	-	-MU164	-MU324

Cat6 KVM Dongle		
		
LCD-A2006 USB-C dongle	LCD-A2005 DP - USB dongle	LCD-A2004 HDMI - USB dongle
		
LCD-A2003 DVI - USB dongle	LCD-A2001 VGA - USB dongle	
Resolution	16:10 - max. 1920 x 1200	
Support ** :	16:9 - max. 1920 x 1080	
	4:3 - max. 1600 x 1200	

Cat6 Combo KVM	IP	Remote	8-port	16-port	32-port
	1	0	-U8KVM2IP	-U16KVM2IP	-U32KVM2IP
	0	1	-U8KVM2	-U16KVM2	-U32KVM2
	0	0	-U8KVM	-U16KVM	-U32KVM



DB-15 Combo KVM	IP	Remote	8-port	16-port
	1	0	-8KVM2IP	-16KVM2IP
	0	1	-8KVM2	-16KVM2
	0	0	-8KVM-u	-16KVM-u

DB-15 VGA USB KVM Cable		
		
LCD-A1014 (6ft)	LCD-A1015 (10ft)	LCD-A1016 (15ft)
Resolution	16:10 - max. 1920 x 1200	
Support ** :	16:9 - max. 1920 x 1080	
	4:3 - max. 1600 x 1200	

DB-15 USB Hub KVM	IP	Remote	8-port
	1	0	-H8KVM2IP
	0	1	-H8KVM2
	0	0	-H8KVM

Standard Keyboard

N keyboard integrated with touchpad



B keyboard integrated with trackball



Supporting layouts

America 
U.S.

EMEA     
U.K. Germany France Spain Italy

Asia  
Japan Korea