

Keyboard Options



- **SQx: iKey 97-Key NEMA 4 Keyboard** USB or 2xPS2
 - Integrated 2 Button Touch-pad and 10-Key Number Pad
- Industrial silicone rubber Continuous Use: 10 million cycles
- Storage: -40°C to +90°C, Operating: -40°C to +70°C
- Optional Red Back-light version (QB)



- **SA2x: Cherry 89-Key Keyboard** USB or 2x PS2
- Integrated 2 Button Optical Trackball
- Gold Crosspoint Contacts, Cherry ML Technology
- Continuous Use, 20 million cycles
- Storage: -40°C to +65°C, Operating: 0°C to +40°C
- MTBF 8.6 Million Hours



- **SI2u: TG3 82-Key Keyboard** USB or 2x PS2
- Integrated 2 Button Glide Pad
- Rubber Membrane Blanket Technology
- Continuous Use, 5 million cycles
- Storage: -40°C to +60°C, Operating: 0°C to +50°C



- **SHx: iKey113-key NEMA 4X keyboard** USB or 2x PS2
- Integrated 3 Button Pointer with Force Sensing Resistor
- Industrial silicone rubber Continuous Use, 10 million cycles
- Storage: -40°C to +70°C, Operating: 20°C to +60°C



- **SMx: Devlin 119-key keyboard** USB or 2x PS2
- Soft feel Tactile ML Switch, Switch Life 50 Million Operations
- Integrated 3 Button Touchpad
- Windows, MAC, SUN and Lynx Operating Systems
- Storage: -40°C to +70°C, Operating: 20°C to +60°C