



www.RackmountMart.com

Benefits

- ▶ 1U 17" LCD console drawer
- ▶ 1280 x 1024 native resolution / 16.7M colors
- ▶ 104-key keyboard with either touchpad or trackball
- ▶ Short depth design of 440mm / 17.3"
- ▶ One Man installation design
- ▶ New enhanced aesthetics with molded front handle

Options

- MAC or SUN Micro keyboard options available
- 2-post rack mounting brackets

Product Specifications

Console Port	
Video input	VGA
KB / MS	Combo (USB or PS2)
VGA console 6ft cable	Drawer end : DB-15 (VGA + USB KB / MS) Server end : VGA + USB type A

LCD Panel	
Panel size (diagonal)	17"
Native resolution	1280 x 1024
Brightness (cd/m ²)	250
Contrast ratio (typ.)	1000:1
Colors	16.7 M
Viewing angle (L/R/U/D)	85/85/80/80
Response time (ms)	5
Dot pitch (mm)	0.264
Display area (mm)	337.92H x 270.33V
Surface treatment	Haze 25%, Hard-coating
Surface hardness	3H
Backlight type	LED
MTBF (hrs)	30,000

Physical		
Product (W x D x H)	Single console	442 x 440 x 44 mm 17.4 x 17.3 x 1.73 inch
Net weight	Single console	12 kg / 26.4 lb

Power		
Input	Auto-sensing 100 to 240VAC, 50 / 60Hz	
Consumption (console / KVM)	Screen on	Max. 25W / Max. 55W
	Power saving mode	Max. 4W / Max. 34W
	Power button on	Max. 1W / Nil


Environment	
Operating temp.	-20 to 65°C degree
Storage temp.	-20 to 60°C degree
Operating humidity	20~90%, non-condensing
Storage humidity	5 ~90%, non-condensing
Operating altitude	16,000 ft
Non-operating altitude	40,000 ft
Shock	10G acceleration (11ms duration)
Vibration	10~300Hz 0.5G RMS random vibration

Compliance	
EMC	FCC, CE & CCC certified
Safety	c UL us, CE / LVD & CCC certified
Environment	RoHS2 & REACH compliant

Standard Keyboard

n keyboard integrated with touchpad

b keyboard integrated with trackball



Supporting layouts

America		United States			
EMEA					
	United Kingdom	Germany	France	Spain	Norway
	Italy	Russia	Switzerland	Netherlands	Portugal
	Asia				
	China	Japan	Korea	Arabia	Turkey

Keyboard Options

* US layout only

Mn Mac keyboard with touchpad



Mb Mac keyboard with trackball

Sn SUN keyboard with touchpad

Sb SUN keyboard with trackball

