



Single Console



**Drawer Features & Display Benefits**



- ▶ 1U 17" or 19" LCD console drawer
- ▶ US compact keyboard layout with either trackball or touchpad
- ▶ Combo interface either PS/2 or USB for single console drawer
- ▶ Enhanced aesthetics with molded front handle and two point lock
- ▶ Slide rails with fixed positions to prevent drawer movement when typing

**Options**

- S-Video + Composite ( BNC ) or Audio input
- HDMI or DVI-D ( either one )
- 17" / 19" Touchscreen : Capacitive, Resistive
- 48V, 24V or 12VDC power

**Specifications**

• **LCD Panel**

Manufacturer :		
Size (diagonal) :	17" TFT	19" TFT
Max resolution :	1280 x 1024	1280 x 1024
Brightness (cd/m2) :	250	250
Backlight :	CCFL	CCFL
Colors :	16.7 M	16.7M
Contrast ratio (typ) :	1000 : 1	1000 : 1
Viewing angle (H/V) :	160° x 160°	160° x 160°
Active area (mm) :	338 x 270	376 x 301
MTBF (hrs) :	50,000	50,000
Signal input :	VGA	VGA

• **Casing Color :** Black ( RAL 9005 )

• **Weight ( Single console )**

Net :	12 kgs ( 26 lbs )	13 kgs ( 29 lbs )
-------	----------------------	----------------------

• **Environmental**

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration ( 11 ms duration )
Vibration :	5~500Hz 1G RMS random vibration

• **Regulatory :** FCC, CE

• **Power**

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 48 Watt, Standby 5 Watt

• **Dimensions ( Single console )**

Product : 441.6 x 700 x 44 mm / 17.4 x 27.6 x 1.73 inch


**Console Cable**

**LCD-A3001**


- 6 feet Combo KVM cable ( bundle )
- VGA + USB or PS/2, server end
  - DB15 ( VGA, USB KB & MS ), console port

**Keyboard**

**t** Compact keyboard integrated with touchpad



**d** Compact keyboard integrated with trackball



**Supporting layouts**

America   
United States