



**Benefits**

- ▶ 1U 16.2" LCD console drawer
- ▶ Dual slide - LCD and keyboard slide independently
- ▶ 1920 x 1200 **WUXGA** native resolution / 16.7M colors ( 8-bit )
- ▶ DVI-D + VGA video input / USB KB / MS
- ▶ 104-key keyboard with touchpad
- ▶ One Man installation design
- ▶ Enhanced aesthetics with molded front handle and two point lock

**Options**

- HDMI 1.4 video input
- 3G / HD / SD-SDI Broadcast-grade input
- Audio input & output
- DC power : 12V / 24V / 48V / 110V / 125V
- MAC or SUN Micro keyboard options available

**Product Specifications**

Console Port	
Video input	VGA + DVI-D single link
KB / MS	USB interface
VGA console 6ft cable or DVI-D console 6ft cable	Drawer end : DB-15 + USB type A x 2 Server end : DB-15 + USB type A x 2  Drawer end : DVI-D + USB type A x 2 Server end : DVI-D + USB type A x 2

Video Option		
Digital	HDMI	HDMI 1.4 / HDCP 1.4

LCD Panel	
Panel size ( diagonal )	16.2"
Native resolution	1920 x 1200
Brightness ( cd/m <sup>2</sup> )	300
Contrast ratio ( typ. )	800 : 1
Colors	16.7 M, 8-bit
Viewing angle ( L/R/U/D )	89/89/89/89
Response time ( ms )	30
Dot pitch ( mm )	0.191
Display area ( mm )	343.8H x 214.9V
Surface treatment	Anti-glare, Hard-coating
Surface hardness	3H
Backlight type	LED
MTBF ( hrs )	20,000

Audio Option		
Input	Connector	3.5mm stereo jack
	Impedance / Power level	30kΩ / 750mV
Output	Connector	3.5mm stereo jack
	Resistance / Power level	30kΩ / 2.8V
Speaker	Dual stereo	2W x 2

Power		
Input	Auto-sensing 100 to 240VAC, 50 / 60Hz	
Consumption (console / KVM)	Screen on	Max. 34W / Max. 59W
	Power saving mode	Max. 4W / Max. 29W
	Power button off	Max. 1W / Nil

Physical		
Product ( W x D x H )	Single console	442 x 650 x 44 mm 17.4 x 25.6 x 1.73 inch
	Console w/ KVM	442 x 650 x 44 mm 17.4 x 25.6 x 1.73 inch
Net weight	Single console	12 kg / 26.4 lb
	Console w/ KVM	13 kg / 28.6 lb

Environment	
Operating temp.	0 to 55°C degree
Storage temp.	-20 to 60°C degree
Operating humidity	20~90%, non-condensing
Storage humidity	5 ~90%, non-condensing
Operating altitude	16,000 ft
Non-operating altitude	40,000 ft
Shock	10G acceleration ( 11ms duration )
Vibration	10~300Hz 0.5G RMS random vibration

\* All dimensions stated are subject to change if options are selected / integrated to base model part codes

Mounting Distance	
Single console drawer / Console w/ KVM drawer	660 ~ 870 mm 26 ~ 34.3 inch


Compliance	
EMC	FCC & CE certified
Safety	CE / LVD certified
Environment	RoHS2 & REACH compliant

\* **IP** console upgrade option for resolution support 1920 x 1080

\*\* Resolution related to LCD specification

<b>2K KVM</b>	<b>IP</b>	Remote	8-port
	0	0	LCD1U17-26-8HD

**2K KVM Cable**



LCD-A3011 (6 ft) DVI-D KVM cable    LCD-A3012 (6 ft) HDMI KVM cable

Resolution Support \*\*:

- 16:9 - max. 2560 x 1440
- 16:10 - max. 1920 x 1200
- 4:3 - max. 1600 x 1200

<b>DVI-D KVM</b>	<b>IP</b>	Remote	12-port
	0	0	LCD1U17-26-12DVI

**DVI-D USB KVM Cable**




Resolution Support \*\*:

- 16:10 - max. 1920 x 1200
- 16:9 - max. 1920 x 1080
- 4:3 - max. 1600 x 1200

LCD-A3005 (6 ft)    LCD-A3006 (15 ft)

<b>Cat6 Combo KVM</b>	<b>IP</b>	Remote	8-port	16-port	32-port
	1	0	LCD1U17-26-U8KVM2IP	LCD1U17-26-U16KVM2IP	LCD1U17-26-U32KVM2IP
	0	1	LCD1U17-26-U8KVM2	LCD1U17-26-U16KVM2	LCD1U17-26-U32KVM2
	0	0	LCD1U17-26-U8KVM	LCD1U17-26-U16KVM	LCD1U17-26-U32KVM

**Cat6 KVM Dongle**



LCD-A2005 DP - USB dongle    LCD-A2004 HDMI - USB dongle    LCD-A2003 DVI - USB dongle

LCD-A2001 VGA - USB dongle    LCD-A2002 VGA - PS/2 dongle


Resolution Support \*\*:

- 16:10 - max. 1920 x 1200
- 16:9 - max. 1920 x 1080
- 4:3 - max. 1600 x 1200

\*\* Resolution related to LCD specification

<b>DB-15 USB Hub KVM</b>	<b>IP</b>	Remote	8-port	16-port
	1	0	LCD1U17-26-H8KVM2IP	LCD1U17-26-H16KVM2IP
	0	1	LCD1U17-26-H8KVM2	LCD1U17-26-H16KVM2
	0	0	LCD1U17-26-H8KVM	LCD1U17-26-H16KVM

**DB-15 VGA USB KVM Cable**



LCD-A1014(6 ft)    LCD-A1015 (10 ft)    LCD-A1016 (15 ft)

Resolution Support :



- 16:10 - max. 1920 x 1200
- 16:9 - max. 1920 x 1080
- 4:3 - max. 1600 x 1200

\*\* Resolution related to LCD specification

<b>DB-15 Matrix KVM</b>	<b>IP</b>	Remote	8-port	16-port
	1	1	LCD1U17-26-M83IP	LCD1U17-26-M163IP
	2	1	LCD1U17-26-M84IP2	LCD1U17-26-M164IP2
	0	1	LCD1U17-26-M82	LCD1U17-26-M162
	0	2	LCD1U17-26-M83	LCD1U17-26-M163
	0	3	LCD1U17-26-M84	LCD1U17-26-M164

**Standard Keyboard**

**N** keyboard integrated with touchpad



**Supporting layouts**

- America**
  - United States
- EMEA**
  - United Kingdom
  - Germany
  - France
  - Spain
  - Norway
- Asia**
  - Italy
  - Russia
  - Switzerland
  - Netherlands
  - Portugal
  - China
  - Japan
  - Korea
  - Arabia
  - Turkey

**Keyboard Options**

\* US layout only

**Mn** Mac keyboard with touchpad



**Sn** S keyboard with touchpad

