



Top View



Front Door
Cool Air In

Rear Door
Hot Air Out



Features & Benefits

- ▶ Easy installation with common tools
- ▶ Thin & light weight design only 4.3 kgs / 9.5 lbs
9 Fan is 5 kgs / 11 lbs
- ▶ Improves extraction of heat from high density cabinet
- ▶ 33U door mount extract / intake fan panel w/ 6 fans
- ▶ Cascade ports for daisy chain up to 16 levels via Cat6 cable
- ▶ Free management software remote access up to 480 fan units
- ▶ Auto & manual CFM setting reduces power consumption
- ▶ 1 x temp. sensor port with a bundled sensor
- ▶ Temperature sensing technology adjusts the fan speeds accordingly
- ▶ Unit or individual fan on / off (remote or local)
- ▶ 48V, 24V or 12VDC power option



Ordering Information

| Model | Installation | Airflow | Purpose |
|---------------------|--------------------|-----------------|------------------------------|
| RA4017-6-R-A | Rear door outside | Extract airflow | Exhaust air out from cabinet |
| RA4017-9-R-A | Front door inside | Intake airflow | Cool air in from aisle |
| RA4017-6-R-B | Front door outside | Intake airflow | Cool air in from aisle |
| RA4017-9-R-B | Rear door inside | Extract airflow | Exhaust air out from cabinet |

* Package includes the material of clear polycarbonate plastic to block off the remaining open perforated area of the door to eliminate bypass air.

Specifications

- **Fan Panel**
 - IP Remote Access : No
 - Daisy Chain Level : From 2nd to 16th level
 - No. of Fans : 6 / 9
 - Individual Fan CFM : 108 CFM
 - Unit CFM (approx.) : 648 CFM / 972 CFM
 - CFM level : Normal / High / Max.
 - Individual Fan on / off : Yes
- **Temperature Sensor**
 - Temp. Port : 1 x temp. sensor port (sensor bundled)
 - Measurement Range : 0 to 99.9°C
 - Measurement Accuracy : +/- 1.5%
 - Temperature Alarm : Yes
- **Environmental**
 - Operating : 0 to 50°C Degree
 - Storage : -5 to 60°C Degree
 - Relative humidity : 5~90%, non-condensing
 - Shock : 50G peak acceleration (11ms, half-sine wave)
 - Vibration : 58~100Hz / 0.98G (11ms / cycle)
- **Power**
 - Input : Auto-sensing
100V or 240V AC at 50 or 60Hz via IEC type cord
 - Consumption : 40W / 60W
- **Casing Color :** Black
- **Mounting :** 33U door mount
- **Safety Regulatory :** FCC & CE certified
- **Environmental :** RoHS2 & REACH compliant by SGS
- **Dimensions**
 - Product : 195 x 42.9 x 1466 mm / 7.7 x 1.7 x 57.7 inch
- **Weight**
 - Net : 6 Fan: 4.3 kgs (9.5 lbs)
9 Fan : 5 kgs (11 lbs)

