


# LCD1U19-017 1U 19" widescreen Rackmount Quad LCD Display

## Drawer Features & Display Benefits

- ▶ 1U 19" widescreen LCD drawer
- ▶ Built-in Quad Display
- ▶ Ideal for CCTV security & industrial control
- ▶ Sliding LCD allowing LCD to remain open when the rack door is closed


**Option** ● DC power : 12V / 24V / 48V / 110 ~ 125V



## Front QD membrane button



## Rear I / O



## Specifications

### • LCD Panel

Manufacturer :	
Size (diagonal) :	19" widescreen TFT
Max resolution :	1440 x 900
Brightness (cd/m2) :	250
Backlight :	LED
Colors :	16.7M
Contrast ratio (typ) :	1000 : 1
Viewing angle (H/V) :	160° x 160°
Active area (mm) :	408 x 255
MTBF (hrs) :	30,000
Signal input :	VGA

• **Power Input :** Auto-sensing 100 to 240VAC, 50 / 60Hz

### • Power Consumption

Screen on :	Max. 25W
Power saving mode :	Max. 4W
Power button on :	Max. 1W

### • Environmental

Operating temperature :	0 to 55°C degree
Storage temperature :	-20 to 60°C degree
Operating humidity :	20~90%, non-condensing
Storage humidity :	5 ~90%, non-condensing
Operating altitude :	16,000 ft
Non-operating altitude :	40,000 ft
Shock :	10G acceleration ( 11ms duration )
Vibration :	5~500Hz 1G RMS random vibration

• **Casing Color :** Black ( RAL 9005 )

### • Regulatory

Safety :	FCC & CE certified
Environmental :	RoHS2 & REACH compliant

### • Weight

Net :	13.5 kgs / 29.7 lbs
-------	---------------------

### • Dimensions

Product :	445 x 650 x 44 mm / 17.5 x 25.6 x 1.73 inch
-----------	---

## Diagrams ( mm )

