



Ultra short depth
400mm / 15.7"



Benefits

- ▶ 1U 17" LCD display drawer
- ▶ 1920 x 1080 native resolution / 16.7M colors (8-bit)
- ▶ HDMI 1.4 + VGA video input (speakers excluded)
- ▶ Ideal for open rack / short depth rack
- ▶ One Man installation design
- ▶ Enhanced aesthetics with molded front panel and two point lock

Options

- Dual stereo speakers for HDMI
- DVI-D + Speakers
- DP 1.0 + Speakers
- Composite + Audio IN + Speakers
- 3G / HD / SD-SDI Broadcast-grade input + Speakers
- DC power : 12V / 24V / 48V / 110V / 125V / 250V
- Touchscreen :
Projected Capacitive 10-pt / Resistive 1-pt

Product Specifications

| Video | |
|-------------|----------------|
| Video input | HDMI 1.4 + VGA |

| Video Option | | |
|--------------|-------------------|-------------------|
| Digital | DVI-D | DVI-D single link |
| | Display port | DP 1.0 / HDCP 1.3 |
| Analog | Composite (BNC) | NTSC & PAL |

| LCD Panel | |
|----------------------------------|--------------------------|
| Panel size (diagonal) | 17.3" |
| Native resolution | 1920 x 1080 |
| Brightness (cd/m ²) | 300 |
| Contrast ratio (typ.) | 1000 : 1 |
| Colors | 16.7 M, 8-bit |
| Viewing angle (L/R/U/D) | 85/85/85/85 |
| Response time (ms) | 25 |
| Dot pitch (mm) | 0.1989 |
| Display area (mm) | 381.888H x 214.812V |
| Surface treatment | Anti-glare, Hard-coating |
| Surface hardness | 3H |
| Backlight type | LED |
| MTBF (hrs) | 15,000 |

| Power | | |
|-------------|---------------------------------------|----------|
| Input | Auto-sensing 100 to 240VAC, 50 / 60Hz | |
| Consumption | Screen on | Max. 14W |
| | Power saving mode | Max. 2W |
| | Power button off | Max. 1W |

| Environment | |
|------------------------|------------------------------------|
| Operating temp. | 0 to 55°C degree |
| Storage temp. | -20 to 60°C degree |
| Operating humidity | 10~90%, non-condensing |
| Storage humidity | 5 ~90%, non-condensing |
| Operating altitude | 16,000 ft |
| Non-operating altitude | 40,000 ft |
| Shock | 10G acceleration (11ms duration) |
| Vibration | 10~300Hz 0.5G RMS random vibration |

| Compliance | |
|-------------|----------------------|
| EMC | FCC & CE |
| Safety | CE / LVD & UKCA |
| Environment | REACH & RoHS3 / WEEE |

| Mounting Distance | |
|-------------------|----------------------------------|
| Display drawer | 410 ~ 640 mm 16.1 ~ 25.2 inch |

| Physical | | |
|-----------------------------|---------|--|
| Dimensions (W x D x H) | Product | 442 x 400 x 44 mm 17.4 x 15.7 x 1.73 inch |
| | Net | 8.7 kg / 19.1 lb |

* All dimensions stated are subject to change if options are selected / integrated to base model part codes

Diagrams (mm)

