



Benefits


- DVI-D KVM with 12 ports in 1U
- Local console & KVM ports support resolution up to 1920 x 1200
- Multi-platform for PC, server, Blade Server & SUN / MAC
- Port switching via front button & keyboard hotkeys
- Hot pluggable, no software or drivers required



Options


- DC power options : 12V / 24V / 48V / 110V / 125V

Basic Models - local console x 1



KVM Port	
Port # :	12
Connector :	DVI-D + USB type B (KB / MS & Analog audio)
Connectivity :	DVI-D + USB KB / MS + Audio 4-in-1 KVM cable (6 / 15 feet)
Resolution :	16:10 - max. 1920 x 1200 / 4:3 - max. 1600 x 1200
Local Console	
Graphic Connector :	1 x DVI-D single link
Input device :	2 x USB type A for keyboard & mouse
Audio out :	1 x 3.5mm stereo audio
Resolution :	16:10 - max. 1920 x 1200 / 4:3 - max. 1600 x 1200

Local console & KVM port connection



Management	
Port switching	Front button & keyboard hotkeys

Power	
Input	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption	Max. 13W

Compatibility	
Hardware	HP / IBM / Dell PC, Server and Blade Server SUN / Mac
OS support	Windows / Linux / Unix / Mac OS

Compliance	
Safety	FCC & CE certified
Environment	RoHS2 & REACH compliant

Environment	
Operating temp.	0 to 55°C degree
Storage temp.	-20 to 60°C degree
Operating humidity	20~90%, non-condensing
Storage humidity	5 ~90%, non-condensing
Operating altitude	16,000 ft
Non-operating altitude	40,000 ft
Shock	10G acceleration (11ms duration)
Vibration	10~300Hz 0.5G RMS random vibration

Physical	
Product (W x D x H)	443 x 171 x 44 mm 17.4 x 6.7 x 1.73 inch
Weight (Net)	2.5 kg / 5.5 lb
Chassis color	Dark
Chassis materials	Steel