

LCD1U17-014 / LCD1U19-013 1U 17", 19" Rackmount SUN LCD Drawer



Drawer Features & Display Benefits

- ▶ 1U 17" or 19" LCD drawer
- ▶ Direct Support for SUN Micro 1152 x 900 native resolution
- ▶ Short depth design of 500mm (19.7")
- ▶ Depth will suit a 600mm rack application
- ▶ Sliding LCD allowing LCD to remain open when the rack door is closed
- ▶ Installation slides for easy, quick installation
- ▶ Enhanced aesthetics with molded front panel and two point lock

Options

- DC power : 12V / 24V / 48V / 110 ~ 125V



Basic I/O : VGA and DVI-D

** For DC power option, casing depth will be extended from 500mm (19.7") to 570mm (22.4")

Specifications

• LCD Panel

	AUO	AUO
Manufacturer :	AUO	AUO
Size (diagonal) :	17" TFT	19" TFT
Max resolution :	1152 x 900 (Direct),	1280 x 1024 (Native)
Brightness (cd/m2) :	250	250
Backlight :	CCFL	LED
Colors :	16.7 M	16.7 M
Contrast ratio (typ) :	1000 : 1	1000 : 1
Viewing angle (H/V) :	160° x 160°	170° x 160°
Active area (mm) :	338 x 270	376 x 301
MTBF (hrs) :	50,000	30,000
Signal input :	VGA or DVI-D	VGA or DVI-D

• Casing Color : Black (RAL 9005)

• Weight

Net :	10.5 kgs (23 lbs)	12.5 kgs (28 lbs)
-------	------------------------	------------------------

• Environmental

Operating :	0 to 55°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration (11 ms duration)
Vibration :	5~500Hz 1G RMS random vibration

• Regulatory

Safety :	FCC & CE certified
Environmental :	RoHS2 & REACH compliant

• Power

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 48 Watt, Standby 5 Watt

• Product Dimensions

LCD1U17-014 :	441.6 x 500 x 44 mm / 17.4 x 19.7 x 1.73 inch
LCD1U19-013 :	441.6 x 500 x 44 mm / 17.4 x 19.7 x 1.73 inch

Diagrams (mm)

