




Basic I/O : HDMI, VGA, Composite, Audio TV w/ Remote controller

Display Features & Benefits

- ▶ 8U rackmount 21.5" widescreen LCD
- ▶ **Full HD** LCD display with 1080p resolution
- ▶ 16.7 million colors displayed in rich
- ▶ Digital TV tuner decodes **ATSC** signal
- ▶ HDMI, VGA, Composite (RCA) connection
- ▶ VESA and Rackmount multiple hole mounting
- ▶ Green LED technology ensures natural colors
- ▶ Modern touch controls



Specifications

• **LCD Panel**

- Manufacturer :
- Size (diagonal) : 21.5" widescreen TFT
- Max resolution : 1920 x 1080
- Brightness (cd/m2) : 250
- Backlight : LED
- Colors : 16.7 M
- Contrast ratio (typ) : 1000 : 1
- Viewing angle (H/V) : 170° x 160°
- Active area (mm) : 477 x 268
- MTBF (hrs) : 30,000
- Signal input : ATSC DTV / HDMI / VGA / Composite

• **Digital TV Tuner**

- Aerial input : 75 ohm coaxial, IEC type
- TV system : ATSC / NTSC

• **Speaker** :

Built-in Dual Stereo Speakers, 2W x 2

• **Power Input** :

Auto-sensing 100 to 240VAC, 50 / 60Hz

• **Power Consumption**

- Screen on : Max. 32W
- Power saving mode : Max. 4W
- Power button on : Max. 1W

• **Environmental**

- Operating temperature : 0 to 55°C degree
- Storage temperature : -20 to 60°C degree
- Operating humidity : 20~90%, non-condensing
- Storage humidity : 5 ~90%, non-condensing
- Operating altitude : 16,000 ft
- Non-operating altitude : 40,000 ft
- Shock : 10G acceleration (11ms duration)
- Vibration : 5~500Hz 1G RMS random vibration

• **Casing Color** :

Black (RAL 9005)

• **Mounting** :

Rackmount, 8U
VESA mount, 100*100mm

• **Regulatory**

- Safety : FCC & CE certified
- Environmental : RoHS2 & REACH compliant

• **Weight**

Net : 10.3 kgs / 22.7 lbs

• **Dimensions**

Product : 501.9 x 64.4 x 353 mm / 19.8 x 2.5 x 13.9 inch

Diagrams (mm)

