


LCD1U19-016 1U 19" Rackmount Quad LCD Display

Drawer Features & Display Benefits

- ▶ 1U 19" LCD drawer
- ▶ Built-in Quad Display
- ▶ Ideal for CCTV security & industrial control
- ▶ Sliding LCD allowing LCD to remain open when the rack door is closed

Option ● 48V, 24V or 12VDC power




FC CE

Front QD membrane button



Rear I/O



Specifications

• LCD Panel

Manufacturer :	
Size (diagonal) :	19" TFT
Max resolution :	1280 x 1024
Brightness (cd/m2) :	250
Backlight :	CCFL
Colors :	16.7M
Contrast ratio (typ) :	1000 : 1
Viewing angle (H/V) :	160° x 160°
Active area (mm) :	376 x 301
MTBF (hrs) :	50,000
Signal input :	VGA

• **Casing Color :** Black (RAL 9005)

• Weight

Net :	12.5 kgs (28 lbs)
-------	------------------------

• Environmental

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration (11 ms duration)
Vibration :	5~500Hz 1G RMS random vibration

• **Regulatory :** FCC, CE

• Power

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 48 Watt, Standby 5 Watt

• Dimensions

Product :	442 x 650 x 44 mm / 17.4 x 25.6 x 1.73 inch
-----------	---

Diagrams (mm)

