

LCDR5U09-01 5U 9" Rackmount Dual LCD Display



24 X 7 X 365

FEATURES

- Industrial Metal Cabinet, Dual Display
- 1024 x 768 Resolution, 350 Nits, 500:1 Contrast Ratio
- BNC Video 2(4) In / 2(4) Out, S-Video 1(2) In, HDMI In 1(2), VGA 1(2) In, Audio 1(2) In, PC Stereo 1(2) In
- 3D Motion Adaptive Deinterlacer
- 1W x 2 Built-In Speakers
- 5U Rack Mounting Form Factor



SPECIFICATIONS

Display	
Screen Size	9.7 Inch
Max. Resolution	1024 x 768 @ 75Hz
Pixel Pitch	0.192 x 0.192mm
Brightness	350cd/m ²
Contrast Ratio	500 : 1
Aspect Ratio	4 : 3
Viewing Angle (H/V)	130° / 140°
Display Color	262,144 colors (8-bit)
Response Time	< 20ms
Video System	NTSC / PAL
Interface	
Video In / Out (BNC Type)	2(4) In / 2(4) Out
HDMI In	1(2) In
S-Video In	1(2) In
VGA In (15Pin D-Sub)	1(2) In
Audio In (RCA Type)	1(2) In
PC Stereo In	1(2) In
Transmitter	
Remote Control	N/A
Audio	
Built-in Speakers	Yes (1W x 2)
Features	
Filter Type	3D Motion Adaptive De-interlacer
LCD Protection Glass	N/A
Multi Language	English, Spanish, French, German, Italian
General	
Outline Dimension (W x H x D)	18.98" x 8.66" x 1.97"
Net Weight	3.4Kg (7.6 lbs)
Material / Color	Electronic galvanized iron / Black
Desk Top Stand	Kick stand / Tilt Back
Consumption: < On	< 35W AC100 ~ 240V(50/60Hz)
Electrical Ratings	DC12V / 3.5A
Operating Temperature	0° ~ 40° C / 32° ~ 104° F
Storage Temperature	-20° ~ 60° C / -4° ~ 140° F
Mounts	
VESA™ Mount Size	75 x 75mm
Wall	SYWB-5, SYWB-10, SYWB-30, SYWB-31
Ceiling	SYCMK-01
Form Factor	5U Rack Mounting
Mount Type	Tiltable Rack Mount


Design and specifications are subject to change without notice

TILT CAPABILITY


LCDR5U09-01 has flexible tiltable rack mount capability



INPUT INTERFACE



DIMENSIONS



OPTIONAL MOUNTS

