



Synergy Global Technology Inc

www.RackmountMart.com


Metered Rack PDU for Blade Servers

Outlets. The PDU has six (6) IEC-320-C19 outlets.

Digital display. A digital display shows aggregate current being used per phase and the current being used per outlet by the PDU.

Power cord. The 1.82-m (6-ft) power cord terminates with a CS8365C connector.

ADH-006-C19-50A-CS



Specifications

Electrical

Input connector	CS8365C 50 A connector
Output connectors	(6) IEC-320-C19
Overload protection	(6) 20 A double-pole breakers
Max output current (outlet)	16 A
Max input current (per phase)	40 A
Cord length	1.83 m (6.00 ft)
Nominal input voltage	200– 240 V, 3-phase
Acceptable input voltage	+6%, –10% of nominal voltage
Input frequency	50/60 Hz

Physical

Dimensions (H × W × D)	927 × 89 × 56 mm (36.50 × 3.50 × 2.20 in)
Shipping dimensions (H × W × D)	1054 × 286 × 70 mm (41.50 × 11.25 × 2.75 in)

Environmental

Elevation (above MSL)	
Operating	3 000 m (10,000 ft)
Storage	15 000 m (50,000 ft)
Temperature	
Operating	–5 to 60° C (23 to 140° F)
Storage	–25 to 65° C (–13 to 149° F)
Humidity	
Operating	5 – 95%, non-condensing
Storage	5 – 95%, non-condensing

Approvals

Safety Certification	UL/cUL Listed, PSE
EMC	FCC: Part 15 Class A ICES-003 Class A VCCI-A

