

Metered Rack Power Distribution Unit

Specifications


Outlets. The Rack PDU has six (6) IEC-320-C13 and twelve (12) IEC-320-C19 locking outlets **2**. (The locking feature is compatible with APC locking input cords and APC locking jumper cords.)

Overcurrent protection. The Rack PDU has six (6) 20 A, UL489 double-pole breakers **1**.

Display interface. The liquid crystal display (LCD) **11** and input buttons **10** allow you to monitor current, power, and voltage measurements of the Rack PDU. Local communication can be established through the serial port **6**, and remote communication through the network port **8**. The USB **5** port allows for firmware upgrades, and the CAN **7** ports enable data transfer for future expansion options. The environmental sensor port **9** allows for monitoring of the temperature and humidity of the room or enclosure.

Power cord. The 1.82-m (6-ft) power cord **3** terminates with an 60 A, 4-pin IEC-309 connector.

Toolless mounting. The Rack PDU has two toolless mounting pegs **4** for 0 U mounting capability in a rack or enclosure.



Specifications

Electrical

Acceptable input voltage	200-240 VAC +6%, -10%, 3-phase
Maximum input current	48 A UL (derated)
Input frequency	50/60 Hz
Input connection	60-A, 4-pin IEC-309
Input power	17.3 kVA UL
Output voltage	200-240 VAC
Maximum output current (outlet)	IEC-320-C13: 12 A; IEC-320-C19: 16 A UL (derated)
Maximum output current (phase)	48 A UL (derated)
Maximum output current (bank)	16 A UL (derated)
Output connections	Six (6) IEC-320-C13 and twelve (12) IEC-320-C19

Physical

Dimensions (H x W x D) (depth does not include toolless pegs)	182.9 x 5.6 x 5.1 cm (72.0 x 2.2 x 2.0 in)
Power cord length	1.82 m (6 ft)
Shipping dimensions (H x W x D)	215 x 22 x 11.3 cm (84.6 x 8.7 x 4.4 in)

Environmental

Maximum elevation (above MSL) Operating/Storage	0–3 000 m (0–10,000 ft) / 0–15 000 m (0–50,000 ft)
Temperature Operating/Storage	–5 to 55° C (23 to 131° F) / –25 to 65° C (–13 to 149° F)
Humidity Operating/Storage	5–95% RH, non-condensing

Compliance

EMC verification	FCC Part 15 Class A, ICES-003 Class A, VCCI-A, EN 55022 Class A, EN 55024, EN 61000-3-2, EN 61000-3-3
Safety verification	UL, cUL