


Switched Rack Power Distribution Unit

Specifications

ASH-024-C-30A-L213




Outlets. The Rack PDU has twenty-one (21) IEC-320-C13 and three (3) IEC-320-C19 locking outlets **2**. A green LED for each outlet turns on when the outlet is energized.

Overcurrent protection. The Rack PDU has three (3) 20 A, 2-pole hydraulic-magnetic circuit breakers **1**.

Display interface. The liquid crystal display (LCD) **3** and input buttons **4** allow you to monitor current, power, and voltage measurements of the Rack PDU. Local communication can be established through the serial port **8**, and remote communication through the network port **5**. The USB **9** and CAN **7** ports enable data transfer for future expansion options. The environmental sensor port **6** allows for monitoring of the temperature and humidity of the room or enclosure.

Power cord. The 2-m (6.0-ft) power cord terminates with a NEMA L21-30P connector **10**.

Toolless mounting. The Rack PDU has two toolless mounting pegs **11** for 0 U mounting capability in a rack or enclosure.



Specifications

Electrical

Acceptable input voltage	208 VAC \pm 10%, 3-phase
Maximum input current (phase)	24 A UL
Input frequency	50/60 Hz
Input connection	NEMA L21-30P
Input power	8.6 kVA UL
Output voltage	208 VAC (Line-to-Line)
Maximum output current (outlet)	IEC-320-C13: 12 A UL IEC-320-C19: 16 A UL
Maximum output current (phase)	24 A UL
Maximum output current (bank)	16 A UL
Output connections	Twenty-one (21) IEC-320-C13; three (3) IEC-320-C19
Overload protection (internal)	Three (3) 20 A, 2-pole hydraulic-magnetic circuit breakers

Physical

Dimensions (H x W x D) (depth does not include toolless pegs)	182.9 x 5.6 x 5.1 cm (72.0 x 2.2 x 2.0 in) Depth at breakers: 8.9 cm (3.5 in)
Power cord length	2 m (6.0 ft)
Shipping dimensions (H x W x D)	204.0 x 16.5 x 12.5 cm (80.3 x 6.5 x 4.9 in)

Environmental

Maximum elevation (above MSL) Operating/Storage	0–3 000 m (0–10,000 ft) / 0–15 000 m (0–50,000 ft)
Temperature Operating/Storage	–5 to 45°C (23 to 115°F) / –25 to 65°C (–13 to 149°F)
Humidity Operating/Storage	5–95% RH, non-condensing

Compliance

EMC verification	FCC Part 15 Class A, ICES-003 Class A
Safety verification	UL



Synergy Global Technology Inc
www.RackmountMart.com