


## Switched Rack PDU

**Outlets.** The PDU has twenty-one (21) IEC-320-C13 outlets (15 A max) and three (3) IEC-320-C19 outlets (16A max).

**Power cord.** The power cord connects the PDU to one power source. The 0.91-m (3-ft) cord terminates with a CS8365C plug.

**Digital Display.** The digital display allows you to monitor the aggregate current of the PDU and to establish a network connection using the network port.

**ASH-024-C-35A-CS**



# Specifications

---

## Electrical

---

Input connector	CS8365C plug
Output connectors	(21) IEC-320-C13 (3) IEC-320-C19 outlets
Cord length	0.91 m (3 ft)
Nominal input voltage	200–240 VAC, 3-phase
Acceptable input voltage	+6%/ -10 % of nominal voltage
Input frequency	50/60 Hz
Output current	15A/C13, 16A/C19; 16A/ bank

---

## Physical

---

Dimensions (H × W × D) <i>(Including breaker box)</i>	1778 × 56 × 45 mm (70.00 × 2.20 × 1.75 in) 1778 × 56 × 89 mm (70.00 × 2.20 × 3.50 in <sup>†</sup> )
Shipping dimensions (H × W × D)	2108 × 114 × 152 mm (83.00 × 4.50 × 6.00 in)

---

---

---

## Environmental

---

Maximum elevation (above MSL)	
Operating	3000 m (10,000 ft)
Storage	15 000 m (50,000 ft)
Temperature	
Operating	–5 to 45° C (23 to 113° F)
Storage	–25 to 65° C (–13 to 149° F)
Humidity	
Operating	5 – 95%, non-condensing
Storage	5 – 95%, non-condensing

---

## Regulatory Approvals

---

EMC	FCC part 15 Class A ICES-003 Class A
Product safety	UL/cUL Listed

---

<sup>†</sup>Depth of 89 mm (3.50 in) is for 191 mm (7.50 in) along the height of the Rack PDU.