



Benefits

- ▶ 1U 20" LCD display drawer
- ▶ 1152 x 900 SUN Micro resolution / 16.7M colors
- ▶ DVI-D + VGA video input
- ▶ Short depth design of 500mm
- ▶ One Man installation design
- ▶ Enhanced aesthetics with molded front panel and two point lock

Options

- DC power : 12V / 24V / 48V / 110V / 125V / 250V
- Touchscreen : Resistive 1-pt

Product Specifications

Video	
Video input	VGA + DVI-D single link

Compliance	
EMC	FCC & CE
Safety	CE / LVD & UKCA
Environment	REACH & RoHS3 / WEEE

LCD Panel	
Panel size (diagonal)	20.1"
Resolution	Direct 1152 x 900 Native 1600 x 1200
Brightness (cd/m ²)	300
Contrast ratio (typ.)	800 : 1
Colors	16.7 M
Viewing angle (L/R/U/D)	89/89/89/89
Response time (ms)	16
Dot pitch (mm)	0.255
Display area (mm)	408H x 306V
Surface treatment	Anti-glare, Hard-coating
Surface hardness	3H
Backlight type	CCFL
MTBF (hrs)	45,000

Mounting Distance	
Display drawer	660 ~ 890 mm 26 ~ 35 inch

Physical		
Dimensions (W x D x H)	Product	440 x 650 x 44 mm 17.3 x 25.6 x 1.73 inch
Weight	Net	13.5 kg / 29.7 lb

* All dimensions stated are subject to change if options are selected / integrated to base model part codes

Power		
Input	Auto-sensing 100 to 240VAC, 50 / 60Hz	
Consumption	Screen on	Max. 45W
	Power saving mode	Max. 2W
	Power button off	Max. 1W

Environment	
Operating temp.	0 to 55°C degree
Storage temp.	-20 to 60°C degree
Operating humidity	10~90%, non-condensing
Storage humidity	5 ~90%, non-condensing
Operating altitude	16,000 ft
Non-operating altitude	40,000 ft
Shock	10G acceleration (11ms duration)
Vibration	10~300Hz 0.5G RMS random vibration

Diagrams (mm)

