


3-Phase 400V 32A switched PDU + outlet measurement : C13 x 12 + C19 x 12



32A model :	Fuse	MCB
VP12C13/12C19-32A-WSi/F_EN/2B-2/LOCK	6	-
VP12C13/12C19-32A-WSi/CR_EN/2B-2/LOCK	-	6

- Input Rating : 32A, 400V
 Inlet : 32A IEC60309 3P+N+E 6hr Red plug
 Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
 Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
 Bank Details : **PH-1** < **Bank 1** > Output 16A max. C 13 # 1-3 (odd) + C 19 # C 1, C 3
 < **Bank 2** > Output 16A max. C 13 # 2-4 (even) + C 19 # C 2, C 4
PH-2 < **Bank 3** > Output 16A max. C 13 # 1-3 (odd) + C 19 # C 1, C 3
 < **Bank 4** > Output 16A max. C 13 # 2-4 (even) + C 19 # C 2, C 4
PH-3 < **Bank 5** > Output 16A max. C 13 # 1-3 (odd) + C 19 # C 1, C 3
 < **Bank 6** > Output 16A max. C 13 # 2-4 (even) + C 19 # C 2, C 4

Three phase switched PDU + outlet measurement

Outlet : 10A Rated IEC320 C13 (lockable) x 12
16A Rated IEC320 C19 (lockable) x 12

Meter Features (WSi Switched PDU + Outlet Measurement)

Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Current (A), Energy (kWh), Voltage (V) & Power factor
 Outlet Measurement : Current (A), Energy (kWh)
 Outlet Control : Outlet Switch ON / OFF
 Accuracy : ±1% true RMS
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified
 Safety Compliance : CE / LVD certified
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing

Dimension : 100 (W) x 90 (D) x 1325 (H) mm
 Material : Steel
 Color : White (outlet bracket)
 Black (chassis)