


PDU specification drawing

3-Phase 400V 32A monitored PDU : C19 x 12



32A model :	Fuse	MCB
VP12C19-32A-W/CR_EN/2B-1/LOCK	-	6

- Input Rating : 32A, 400V
 Inlet : 32A IEC60309 3P+N+E 6hr Red plug
 Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
 Protection : 16A single pole hydraulic MCB x 6
 Bank Details : **PH-1** < **Bank 1** > Output 16A max. C 19 # C 1 - C 2
 < **Bank 2** > Output 16A max. C 19 # C 3 - C 4
 PH-2 < **Bank 3** > Output 16A max. C 19 # C 1 - C 2
 < **Bank 4** > Output 16A max. C 19 # C 3 - C 4
 PH-3 < **Bank 5** > Output 16A max. C 19 # C 1 - C 2
 < **Bank 6** > Output 16A max. C 19 # C 3 - C 4

Three phase monitored PDU

Outlet : 16A Rated IEC320 C19 (lockable) x 12

Meter Features (W monitored PDU)

- Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
 Accuracy : ±1% true RMS
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
 Safety Compliance : CE / LVD certified
 Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing

- Dimension : 70 (W) x 83 (D) x 1425 (H) mm
 Material : Extrusion
 Color : Black