


# PDU specification drawing

## 3-Phase 400V 16A monitored PDU : C19 x 12



16A model :	Fuse	MCB
VP12C19-16A-W/CR_EN/2B-1/LOCK	-	<b>3</b>

Input Rating : 16A, 400V  
 Inlet : 16A IEC60309 3P+N+E 6hr Red plug  
 Cordset : 5-wire 2 meter 1.5mm sq. H07RN-F cordset  
 Protection : 16A single pole hydraulic MCB x 3  
 Phase Details : < **PH-1** > Output 16A max. C 1 9 # C 1 - C 4  
                   < **PH-2** > Output 16A max. C 1 9 # C 1 - C 4  
                   < **PH-3** > Output 16A max. C 1 9 # C 1 - C 4

### Three phase monitored PDU

Outlet : 16A Rated IEC320 C19 (lockable) x 12

### Meter Features ( W monitored PDU )

Local Display : Field replaceable 2.8" color LCD with touchscreen  
 Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor  
 Accuracy : ±1% true RMS  
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels  
 Cascade : Up to 16 PDU under single IP address via IP dongle  
 SNMP : via IP dongle  
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified  
 Safety Compliance : CE / LVD certified  
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

Dimension : 70 (W) x 83 (D) x 1425 (H) mm  
 Material : Extrusion  
 Color : Black