


PDU specification drawing

3-Phase 400V 16A monitored PDU : C13 x 18 + C19 x 12



16A model :	Fuse	MCB
VP18C13/12C19-16A-W/F_EN/2B-2	3	-
VP18C13/12C19-16A-W/CR_EN/2B-2	-	3

Input Rating : 16A, 400V  
Inlet : 16A IEC60309 3P+N+E 6hr Red plug  
Cordset : 5-wire 2 meter 1.5mm sq. H07RN-F cordset  
Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 3  
Phase Details : < PH-1 > Output 16A max. C 13 # 1 - 6 + C 19 # C1 - C4  
< PH-2 > Output 16A max. C 13 # 1 - 6 + C 19 # C1 - C4  
< PH-3 > Output 16A max. C 13 # 1 - 6 + C 19 # C1 - C4

Three phase monitored PDU

Outlet : 10A Rated IEC320 C13 x 18  
16A Rated IEC320 C19 x 12



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.  
Copyright 2015 Synergy Global Technology Inc. All rights reserved.

Meter Features ( W monitored PDU )

Local Display : Field replaceable 2.8" color LCD with touchscreen  
Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor  
Accuracy : ±1% true RMS  
IP Access : via IP dongle, one IP Access up to 16 PDU Levels  
Cascade : Up to 16 PDU under single IP address via IP dongle  
SNMP : via IP dongle  
Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified  
Safety Compliance : CE / LVD certified  
Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C  
Storage Temperature : -25 to 65 °C  
Operating Altitude : 0 to 2,000 m  
Storage Altitude : 0 to 15,000 m  
Humidity : 8 to 95% RH, non-condensing

Dimension : 78 (W) x 70 (D) x 1550 (H) mm  
Material : Steel  
Color : White ( outlet bracket )  
Black ( chassis )