



32A model :	Fuse	MCB
VP18C13/6C19-32A-Wi/F_EN/2B-2	6	-
VP18C13/6C19-32A-Wi/CR_EN/2B-2	-	6

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
- Bank Details :
 - PH-1 < Bank 1 > Output 16A max. C 13 # 1-5 (odd) + C 19 # C 1
 - < Bank 2 > Output 16A max. C 13 # 2-6 (even) + C 19 # C 2
 - PH-2 < Bank 3 > Output 16A max. C 13 # 1-5 (odd) + C 19 # C 1
 - < Bank 4 > Output 16A max. C 13 # 2-6 (even) + C 19 # C 2
 - PH-3 < Bank 5 > Output 16A max. C 13 # 1-5 (odd) + C 19 # C 1
 - < Bank 6 > Output 16A max. C 13 # 2-6 (even) + C 19 # C 2

Three phase monitored PDU + outlet measurement

Outlet : 10A Rated IEC320 C13 x 18
16A Rated IEC320 C19 x 6

Meter Features (Wi Monitored PDU + Outlet Measurement)

- Local Display : Field replaceable 2.8" color LCD with touchscreen
- Bank Measurement : Current (A), Energy (kWh), Voltage (V) & Power factor
- Outlet Measurement : Current (A), Energy (kWh)
- Accuracy : ±1% true RMS
- IP Access : via IP dongle, one IP Access up to 16 PDU Levels
- Cascade : Up to 16 PDU under single IP address via IP dongle
- SNMP : via IP dongle
- Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
- Safety Compliance : CE / LVD certified
- Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
- Storage Temperature : -25 to 65 °C
- Operating Altitude : 0 to 2,000 m
- Storage Altitude : 0 to 15,000 m
- Humidity : 8 to 95% RH, non-condensing

- Dimension : 85 (W) x 90 (D) x 1325 (H) mm
- Material : Steel
- Color : White (outlet bracket)
Black (chassis)

