


## 3-Phase 400V 32A switched PDU + outlet measurement : C13 x 18



32A model :	Fuse	MCB
VP18C13-32A-WSi/F_EN/2B-2	6	-
VP18C13-32A-WSi/CR_EN/2B-2	-	6

- Input Rating : 32A, 400V  
 Inlet : 32A IEC60309 3P+N+E 6hr Red plug  
 Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset  
 Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6  
 Bank Details : **PH-1** < **Bank 1** > Output 16A max. C 13 # 1-5 (odd)  
                   < **Bank 2** > Output 16A max. C 13 # 2-6 (even)  
**PH-2** < **Bank 3** > Output 16A max. C 13 # 1-5 (odd)  
                   < **Bank 4** > Output 16A max. C 13 # 2-6 (even)  
**PH-3** < **Bank 5** > Output 16A max. C 13 # 1-5 (odd)  
                   < **Bank 6** > Output 16A max. C 13 # 2-6 (even)

### Three phase switched PDU + outlet measurement

Outlet : 10A Rated IEC320 C13 x 18

### Meter Features ( WSi Switched PDU + Outlet Measurement )

- Local Display : Field replaceable 2.8" color LCD with touchscreen  
 Bank Measurement : Current ( A ), Energy ( kWh ), Voltage ( V ) & Power factor  
 Outlet Measurement : Current ( A ), Energy ( kWh )  
 Outlet Control : Outlet Switch ON / OFF  
 Accuracy : ±1% true RMS  
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels  
 Cascade : Up to 16 PDU under single IP address via IP dongle  
 SNMP : via IP dongle  
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified  
 Safety Compliance : CE / LVD certified  
 Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

- Dimension : 85 (W) x 90 (D) x 1325 (H) mm  
 Material : Steel  
 Color : White ( outlet bracket )  
           Black ( chassis )