


## 3-Phase 400V 16A individual fused switched PDU : C13 x 21 + C19 x 3



16A model :	Fuse	MCB
VP21C13/3C19-16A-WS/GF/F_EN/2B-2	3	-
VP21C13/3C19-16A-WS/GF/CR_EN/2B-2	-	3

Input Rating : 16A, 400V  
 Inlet : 16A IEC60309 3P+N+E 6hr Red plug  
 Cordset : 5-wire 2 meter 1.5mm sq. H07RN-F cordset  
 Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 3  
 Phase Details : < PH-1 > Output 16A max. C 13 # 1-7 + C 19 # C 1  
 < PH-2 > Output 16A max. C 13 # 1-7 + C 19 # C 1  
 < PH-3 > Output 16A max. C 13 # 1-7 + C 19 # C 1

### Three phase switched PDU

Outlet : 10A Rated IEC320 C13 with 5A individual fuse x 21  
 16A Rated IEC320 C19 with 5A individual fuse x 3



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.  
 Copyright 2015 Synergy Global Technology Inc. All rights reserved.

### Meter Features ( WS Switched PDU )

Local Display : Field replaceable 2.8" color LCD with touchscreen  
 Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor  
 Outlet Control : Outlet Switch ON / OFF  
 Accuracy : ±1% true RMS  
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels  
 Cascade : Up to 16 PDU under single IP address via IP dongle  
 SNMP : via IP dongle  
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified  
 Safety Compliance : CE / LVD certified  
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

Dimension : 100 (W) x 90 (D) x 1325 (H) mm  
 Material : Steel  
 Color : White ( outlet bracket )  
 Black ( chassis )