


# PDU specification drawing

## 3-Phase 400V 32A monitored PDU : SCH x 18



32A model :	Fuse	MCB
VP18SCH-32A-W/CR_EN/2B-1	-	6

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A single pole hydraulic MCB x 6
- Bank Details : **PH-1** < **Bank 1** > Output 16A max. SCH # 1 - 3  
                   < **Bank 2** > Output 16A max. SCH # 4 - 6
- PH-2** < **Bank 3** > Output 16A max. SCH # 1 - 3  
                   < **Bank 4** > Output 16A max. SCH # 4 - 6
- PH-3** < **Bank 5** > Output 16A max. SCH # 1 - 3  
                   < **Bank 6** > Output 16A max. SCH # 4 - 6

**Three phase monitored PDU**  
Outlet : 16A Rated Schuko x 18

**Meter Features ( W monitored PDU )**

- Local Display : Field replaceable 2.8" color LCD with touchscreen
- Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor
- Accuracy : ±1% true RMS
- IP Access : via IP dongle, one IP Access up to 16 PDU Levels
- Cascade : Up to 16 PDU under single IP address via IP dongle
- SNMP : via IP dongle
- Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
- Safety Compliance : CE / LVD certified
- Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
- Storage Temperature : -25 to 65 °C
- Operating Altitude : 0 to 2,000 m
- Storage Altitude : 0 to 15,000 m
- Humidity : 8 to 95% RH, non-condensing

- Dimension : 70 (W) x 83 (D) x 1650 (H) mm
- Material : Extrusion
- Color : Black