


3-Phase 400V 32A individual fused monitored PDU + outlet measurement : C13 x 21 + C19 x 3



32A model :	Fuse	MCB
VP21C13/3C19-32A-Wi/GF/F_EN/2B-2	6	-
VP21C13/3C19-32A-Wi/GF/CR_EN/2B-2	-	6

- Input Rating : 32A, 400V
 Inlet : 32A IEC60309 3P+N+E 6hr Red plug
 Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
 Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
 Bank Details : **PH-1** < **Bank 1** > Output 16A max. C 13 # 1 - 7 (odd)
 < **Bank 2** > Output 16A max. C 13 # 2-6 (even) + C 19 # C 1
PH-2 < **Bank 3** > Output 16A max. C 13 # 1 - 7 (odd)
 < **Bank 4** > Output 16A max. C 13 # 2-6 (even) + C 19 # C 1
PH-3 < **Bank 5** > Output 16A max. C 13 # 1 - 7 (odd)
 < **Bank 6** > Output 16A max. C 13 # 2-6 (even) + C 19 # C 1

Three phase monitored PDU + outlet measurement

Outlet : 10A Rated IEC320 C13 with 5A individual fuse x 21
 16A Rated IEC320 C19 with 5A individual fuse x 3



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.

Copyright 2015 Synergy Global Technology Inc. All rights reserved.

Meter Features (Wi Monitored PDU + Outlet Measurement)

- Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Current (A), Energy (kWh), Voltage (V) & Power factor
 Outlet Measurement : Current (A), Energy (kWh)
 Accuracy : ±1% true RMS
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
 Safety Compliance : CE / LVD certified
 Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing

- Dimension : 100 (W) x 90 (D) x 1325 (H) mm
 Material : Steel
 Color : White (outlet bracket)
 Black (chassis)