



32A model :	Fuse	MCB
VP30C13/6C19-32A-WSi/F_EN/2B-2/LOCK	6	-
VP30C13/6C19-32A-WSi/CR_EN/2B-2/LOCK	-	6

- Input Rating : 32A, 400V
 Inlet : 32A IEC60309 3P+N+E 6hr Red plug
 Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
 Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
 Bank Details : **PH-1 < Bank 1 >** Output 16A max. C 13 # 1-9 (odd) + C 19 # C1
 < Bank 2 > Output 16A max. C 13 # 2-10 (even) + C 19 # C2
PH-2 < Bank 3 > Output 16A max. C 13 # 1-9 (odd) + C 19 # C1
 < Bank 4 > Output 16A max. C 13 # 2-10 (even) + C 19 # C2
PH-3 < Bank 5 > Output 16A max. C 13 # 1-9 (odd) + C 19 # C1
 < Bank 6 > Output 16A max. C 13 # 2-10 (even) + C 19 # C2

Three phase switched PDU + outlet measurement

Outlet : 10A Rated IEC320 C13 (lockable) x 30
16A Rated IEC320 C19 (lockable) x 6

Meter Features (WSi Switched PDU + Outlet Measurement)

- Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Current (A), Energy (kWh), Voltage (V) & Power factor
 Outlet Measurement : Current (A), Energy (kWh)
 Outlet Control : Outlet Switch ON / OFF
 Accuracy : ±1% true RMS
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
 Safety Compliance : CE / LVD certified
 Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing

- Dimension : 100 (W) x 90 (D) x 1700 (H) mm
 Material : Steel
 Color : White (outlet bracket)
 Black (chassis)