


3-Phase 400V 63A monitored PDU : C13 x 24 + C19 x 6



63A model :	Fuse	MCB
VP24C13/6C19-63A-W/CR_EN/2B-2	-	6

- Input Rating : 63A, 400V
- Inlet : 63A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 10.0mm sq. H07RN-F cordset
- Protection : 30A single pole hydraulic MCB x 6
- Bank Details :
 - PH-1 < Bank 1 >** Output 30A max. C 13 # 1-7 (odd) + C 19 # C 1
 - < Bank 2 >** Output 30A max. C 13 # 2-8 (even) + C 19 # C 2
 - PH-2 < Bank 3 >** Output 30A max. C 13 # 1-7 (odd) + C 19 # C 1
 - < Bank 4 >** Output 30A max. C 13 # 2-8 (even) + C 19 # C 2
 - PH-3 < Bank 5 >** Output 30A max. C 13 # 1-7 (odd) + C 19 # C 1
 - < Bank 6 >** Output 30A max. C 13 # 2-8 (even) + C 19 # C 2

Three phase monitored PDU

Outlet : 10A Rated IEC320 C13 x 24
16A Rated IEC320 C19 x 6



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.
Copyright 2015 Synergy Global Technology Inc. All rights reserved.

Meter Features (W monitored PDU)

- Local Display : Field replaceable 2.8" color LCD with touchscreen
- Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
- Accuracy : ±1% true RMS
- IP Access : via IP dongle, one IP Access up to 16 PDU Levels
- Cascade : Up to 16 PDU under single IP address via IP dongle
- SNMP : via IP dongle
- Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
- Safety Compliance : CE / LVD certified
- Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
- Storage Temperature : -25 to 65 °C
- Operating Altitude : 0 to 2,000 m
- Storage Altitude : 0 to 15,000 m
- Humidity : 8 to 95% RH, non-condensing

- Dimension : 100 (W) x 70 (D) x 1550 (H) mm
- Material : Steel
- Color : White (outlet bracket)
Black (chassis)