


PDU specification drawing

3-Phase 400V 63A monitored PDU : C13 x 30



63A model :	Fuse	MCB
VP30C13-63A-W/CR_EN/2B-2	-	6

- Input Rating : 63A, 400V
 Inlet : 63A IEC60309 3P+N+E 6hr Red plug
 Cordset : 5-wire 2 meter 10.0mm sq. H07RN-F cordset
 Protection : 30A single pole hydraulic MCB x 6
 Bank Details : **PH-1** < **Bank 1** > Output 30A max. C 13 # 1-9 (odd)
 < **Bank 2** > Output 30A max. C 13 # 2-10 (even)
PH-2 < **Bank 3** > Output 30A max. C 13 # 1-9 (odd)
 < **Bank 4** > Output 30A max. C 13 # 2-10 (even)
PH-3 < **Bank 5** > Output 30A max. C 13 # 1-9 (odd)
 < **Bank 6** > Output 30A max. C 13 # 2-10 (even)

Three phase monitored PDU
 Outlet : 10A Rated IEC320 C13 x 30

Meter Features (W monitored PDU)

- Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
 Accuracy : ±1% true RMS
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
 Safety Compliance : CE / LVD certified
 Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing

- Dimension : 100 (W) x 70 (D) x 1550 (H) mm
 Material : Steel
 Color : White (outlet bracket)
 Black (chassis)