



16A model :	Fuse	MCB
VP24C13/6C19-16A-Wi/F_EN/2B-2	3	-
VP24C13/6C19-16A-Wi/CR_EN/2B-2	-	3

Input Rating : 16A, 400V
 Inlet : 16A IEC60309 3P+N+E 6hr Red plug
 Cordset : 5-wire 2 meter 1.5mm sq. H07RN-F cordset
 Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 3
 Phase Details : < PH-1 > Output 16A max. C 13 # 1-8 + C 19 # C1-C2
 < PH-2 > Output 16A max. C 13 # 1-8 + C 19 # C1-C2
 < PH-3 > Output 16A max. C 13 # 1-8 + C 19 # C1-C2

Three phase monitored PDU + outlet measurement

Outlet : 10A Rated IEC320 C13 x 24
 16A Rated IEC320 C19 x 6



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.
 Copyright 2015 Synergy Global Technology Inc. All rights reserved.

Meter Features (Wi Monitored PDU + Outlet Measurement)

Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Current (A), Energy (kWh), Voltage (V) & Power factor
 Outlet Measurement : Current (A), Energy (kWh)
 Accuracy : ±1% true RMS
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified
 Safety Compliance : CE / LVD certified
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing

Dimension : 85 (W) x 90 (D) x 1700 (H) mm
 Material : Steel
 Color : White (outlet bracket)
 Black (chassis)