


# PDU specification drawing

## 3-Phase 400V 63A monitored PDU : C19 x 24



63A model :	Fuse	MCB
VP24C19-63A-W/CR_EN/2B-2	-	6

- Input Rating : 63A, 400V
- Inlet : 63A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 10.0mm sq. H07RN-F cordset
- Protection : 30A single pole hydraulic MCB x 6
- Bank Details :
  - PH-1 < Bank 1 >** Output 30A max. C 19 # C1 - C7 (odd)
  - < Bank 2 >** Output 30A max. C 19 # C2 - C8 (even)
  - PH-2 < Bank 3 >** Output 30A max. C 19 # C1 - C7 (odd)
  - < Bank 4 >** Output 30A max. C 19 # C2 - C8 (even)
  - PH-3 < Bank 5 >** Output 30A max. C 19 # C1 - C7 (odd)
  - < Bank 6 >** Output 30A max. C 19 # C2 - C8 (even)

**Three phase monitored PDU**  
Outlet : 16A Rated IEC320 C19 x 24

**Meter Features ( W monitored PDU )**

- Local Display : Field replaceable 2.8" color LCD with touchscreen
- Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor
- Accuracy : ±1% true RMS
- IP Access : via IP dongle, one IP Access up to 16 PDU Levels
- Cascade : Up to 16 PDU under single IP address via IP dongle
- SNMP : via IP dongle
- Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
- Safety Compliance : CE / LVD certified
- Environment Compliance : RoHS2 & REACH
- Operating Temperature : -5 to 60 °C
- Storage Temperature : -25 to 65 °C
- Operating Altitude : 0 to 2,000 m
- Storage Altitude : 0 to 15,000 m
- Humidity : 8 to 95% RH, non-condensing
- Dimension : 100 (W) x 70 (D) x 1550 (H) mm
- Material : Steel
- Color : White ( outlet bracket )  
Black ( chassis )

