


PDU specification drawing

3-Phase 400V 32A switched PDU : C19 x 24



| 32A model : | Fuse | MCB |
|---------------------------|------|-----|
| VP24C19-32A-WS/F_EN/2B-2 | 6 | - |
| VP24C19-32A-WS/CR_EN/2B-2 | - | 6 |

Input Rating : 32A, 400V
Inlet : 32A IEC60309 3P+N+E 6hr Red plug
Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
Bank Details : **PH-1** < **Bank 1** > Output 16A max. C 19 # C 1 - C 7 (odd)
< **Bank 2** > Output 16A max. C 19 # C 2 - C 8 (even)
PH-2 < **Bank 3** > Output 16A max. C 19 # C 1 - C 7 (odd)
< **Bank 4** > Output 16A max. C 19 # C 2 - C 8 (even)
PH-3 < **Bank 5** > Output 16A max. C 19 # C 1 - C 7 (odd)
< **Bank 6** > Output 16A max. C 19 # C 2 - C 8 (even)

Three phase switched PDU

Outlet : 16A Rated IEC320 C19 x 24



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.
Copyright 2015 Synergy Global Technology Inc. All rights reserved.

Meter Features (WS Switched PDU)

Local Display : Field replaceable 2.8" color LCD with touchscreen
Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
Outlet Control : Outlet Switch ON / OFF
Accuracy : ±1% true RMS
IP Access : via IP dongle, one IP Access up to 16 PDU Levels
Cascade : Up to 16 PDU under single IP address via IP dongle
SNMP : via IP dongle
Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified
Safety Compliance : CE / LVD certified
Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C
Storage Temperature : -25 to 65 °C
Operating Altitude : 0 to 2,000 m
Storage Altitude : 0 to 15,000 m
Humidity : 8 to 95% RH, non-condensing

Dimension : 85 (W) x 90 (D) x 1700 (H) mm
Material : Steel
Color : White (outlet bracket)
Black (chassis)