



**FEATURES**

- 103 Key compact keyboard with mouse storage and use area in 1U of vertical 19" rack space.
- Mounted with included smooth action ball bearing slides which lock in the extended position.
- Convenient area in back of keyboard for easy mouse use, mouse stores behind keyboard.
- Retainer and lock options to keep unit contained in the rack when not in use.
- Housed in rugged steel construction with a durable powder coat finish.

**KEYBOARD SPECIFICATIONS**

<b>Keys:</b>	103 keys with Windows key
<b>Rollover:</b>	Alpha N-key rollover.
<b>Auto repeat:</b>	Yes.
<b>Self Diagnostics:</b>	Yes
<b>Reliability:</b>	5M switch life cycles.
<b>Pointing Device:</b>	Optional Optical Mouse (M)
<b>Interface:</b>	USB


**GENERAL SPECIFICATIONS**

<b>Dimensions:</b>	19.0" (W) x 1.75" (H) x 20.00" (D) (22.75 D w/Cable Management)
<b>Slides:</b>	18" (20" extension) Adjustable for 20.5" to 31.5" mounting depth.
<b>Weight:</b>	15 lbs
<b>Temperature:</b>	Operating: 0°C to 50°C Storage: -40°C to 60°C
<b>Humidity:</b>	Operating: 20 to 90% RH Non Condensing (max)
<b>Color:</b>	Black

Specifications subject to change without notice.

**MODEL NUMBER**

LCDK1066-b-bk-



Additional options and configurations available.

