


3-Phase 400V 32A individual fused monitored PDU + outlet measurement : C13 x 30 + C19 x 6



32A model :	Fuse	MCB
VP30C13/6C19-32A-Wi/GF/F_EN/2B-2	6	-
VP30C13/6C19-32A-Wi/GF/CR_EN/2B-2	-	6

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
- Bank Details :
 - PH-1 < Bank 1 >** Output 16A max. C13 #1-9(odd) + C19 #C1
 - < Bank 2 >** Output 16A max. C13 #2-10(even) + C19 #C2
 - PH-2 < Bank 3 >** Output 16A max. C13 #1-9(odd) + C19 #C1
 - < Bank 4 >** Output 16A max. C13 #2-10(even) + C19 #C2
 - PH-3 < Bank 5 >** Output 16A max. C13 #1-9(odd) + C19 #C1
 - < Bank 6 >** Output 16A max. C13 #2-10(even) + C19 #C2

Three phase monitored PDU + outlet measurement

Outlet : 10A Rated IEC320 C13 with 5A individual fuse x 30
16A Rated IEC320 C19 with 5A individual fuse x 6

Meter Features (Wi Monitored PDU + Outlet Measurement)

Local Display : Field replaceable 2.8" color LCD with touchscreen
Bank Measurement : Current (A), Energy (kWh), Voltage (V) & Power factor
Outlet Measurement : Current (A), Energy (kWh)
Accuracy : ±1% true RMS
IP Access : via IP dongle, one IP Access up to 16 PDU Levels
Cascade : Up to 16 PDU under single IP address via IP dongle
SNMP : via IP dongle
Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified
Safety Compliance : CE / LVD certified
Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C
Storage Temperature : -25 to 65 °C
Operating Altitude : 0 to 2,000 m
Storage Altitude : 0 to 15,000 m
Humidity : 8 to 95% RH, non-condensing

Dimension : 100 (W) x 90 (D) x 1700 (H) mm
Material : Steel
Color : White (outlet bracket)
Black (chassis)