


PDU specification drawing

3-Phase 400V 63A monitored PDU : C13 x 36



63A model :	Fuse	MCB
VP36C13-63A-W/CR_EN/2B-2	-	6

- Input Rating : 63A, 400V
 Inlet : 63A IEC60309 3P+N+E 6hr Red plug
 Cordset : 5-wire 2 meter 10.0mm sq. H07RN-F cordset
 Protection : 30A single pole hydraulic MCB x 6
 Bank Details : **PH-1 < Bank 1 >** Output 30A max. C 13 # 1-11 (odd)
 < Bank 2 > Output 30A max. C 13 # 2-12 (even)
PH-2 < Bank 3 > Output 30A max. C 13 # 1-11 (odd)
 < Bank 4 > Output 30A max. C 13 # 2-12 (even)
PH-3 < Bank 5 > Output 30A max. C 13 # 1-11 (odd)
 < Bank 6 > Output 30A max. C 13 # 2-12 (even)

Three phase monitored PDU
 Outlet : 10A Rated IEC320 C13 x 36



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.
 Copyright 2015 Synergy Global Technology Inc. All rights reserved.

Meter Features (W monitored PDU)

- Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
 Accuracy : ±1% true RMS
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- | | |
|--------------------------|---|
| EMC Compliance : | FCC & CE certified |
| Safety Compliance : | CE / LVD certified |
| Environment Compliance : | RoHS2 & REACH |
| Operating Temperature : | -5 to 60 °C |
| Storage Temperature : | -25 to 65 °C |
| Operating Altitude : | 0 to 2,000 m |
| Storage Altitude : | 0 to 15,000 m |
| Humidity : | 8 to 95% RH, non-condensing |
| Dimension : | 100 (W) x 70 (D) x 1550 (H) mm |
| Material : | Steel |
| Color : | White (outlet bracket)
Black (chassis) |