


# ID-H17A 17" SunReadable Front Aluminum LCD Panel

## Dimension Drawings (mm)



### Applications

- Industrial process control
- Point of sales / Kiosk
- Security / Surveillance
- Touchscreen display panel


### Options

- Touchscreen
- S-Video, RCA & BNC & DVI
- DC power input ( 12 / 24 / 48 VDC )
- Audio input with speaker
- TV tuner with remote controller
- Standard remote controller for AV, VGA, DVI input
- NEMA4 / IP65 2mm Protective Glass

### Design features

- SunReadable LCD panel
- 800 cd/m<sup>2</sup> industrial brightness
- 6mm aluminum front bezel with 45° chamfer
- OSD control keys to optimize the display

## Specifications

LCD Panel	 Class A TFT LCD panel	Operating Temperature	0° to 50° C
Panel Grading	Class A TFT LCD panel	Storage Temperature	-5° to 60° C
Panel Size (in.)	17"	Humidity	5~90%, non-condensing
Optimum Resolution	1280 x 1024	Shock	10G peak acceleration (11ms duration)
Display Color	16.2M	Vibration	5-500Hz, 1G RMS random vibration
Brightness-nits (cd/m <sup>2</sup> )	800		
Contrast Ratio	500 : 1		
Pixel Pitch (mm)	0.264 x 0.264		
Viewing Angle (L/R/U/D)	70 / 70 / 70 / 60		
OSD Control	Brightness, Contrast, Phase & Clock, Color, H & V position, Auto-tune & Recall		
Connector(s)	D-Sub 15 pin VGA analog		
LCD Panel MTBF (hrs)	50,000		
Power	100~240VAC via AC adapter		
Mounting	VESA-mount, Mounting bracket and Optional OEM mounting design		
Dimensions (mm)	415 x 57 x 328 (W x D x H)		
		<b>Ordering information</b>	
		Model no.	Description
		ID-H17A	17" SunReadable front aluminum LCD panel w/ VGA input
		ID-H17AAV	17" SunReadable front AI. LCD w/ VGA,S-Video+RCA input
		ID-H17ADVI	17" SunReadable front AI. LCD w/ VGA, DVI input
		ID-H17ABNC	17" SunReadable front AI. LCD w/ VGA,S-Video+BNC input
		ID-H17ADC12	17" SunReadable front AI. LCD w/ VGA input, 12V DC input
		ID-H17ADC24	17" SunReadable front AI. LCD w/ VGA input, 24V DC input
		ID-H17ADC48	17" SunReadable front AI. LCD w/ VGA input, 48V DC input
		-IP65	Add NEMA4 / IP65 Protective Glass