


ID-H19A 19" SunReadable Front Aluminum LCD Panel

Dimension Drawings (mm)



Applications

- Industrial process control
- Point of sales / Kiosk
- Security / Surveillance
- Touchscreen display panel

Options

- Touchscreen
- S-Video, RCA & BNC & DVI
- DC power input (12 / 24 / 48 VDC)
- Audio input with speaker
- TV tuner with remote controller
- Standard remote controller for AV, VGA, DVI input

Design features

- SunReadable LCD panel
- 800 cd/m2 industrial brightness
- 6mm aluminum front bezel with 45° chamfer
- OSD control keys to optimize the display

Specifications

LCD Panel

Panel Grading	Class A TFT LCD panel
Panel Size (in.)	19"
Optimum Resolution	1280 x 1024
Display Color	16.7M
Brightness-nits (cd/m ²)	800
Contrast Ratio	800 : 1
Pixel Pitch (mm)	0.294 x 0.294
Viewing Angle (L/R/U/D)	80 / 80 / 80 / 80
OSD Control	Brightness, Contrast, Phase & Clock, Color, H & V position, Auto-tune & Recall
Connector(s)	D-Sub 15 pin VGA analog
LCD Panel MTBF (hrs)	50,000
Power	100~240VAC via AC adapter
Mounting	VESA-mount, Mounting bracket and Optional OEM mounting design
Dimensions (mm)	471 x 63 x 393 (W x D x H)



Operating Temperature

0° to 50° C

Storage Temperature

-5° to 60° C

Humidity

5~90%, non-condensing

Shock

10G peak acceleration
(11ms duration)

Vibration

5-500Hz, 1G RMS random vibration

Ordering information

Model no.	Description
ID-H19A	19" SunReadable front aluminum LCD panel w/ VGA input
ID-H19AAV	19" SunReadable front AI. LCD w/ VGA,S-Video+RCA input
ID-H19ADVI	19" SunReadable front AI. LCD w/ VGA, DVI input
ID-H19ABNC	19" SunReadable front AI. LCD w/ VGA,S-Video+BNC input
ID-H19ADC12	19" SunReadable front AI. LCD w/ VGA input, 12V DC input
ID-H19ADC24	19" SunReadable front AI. LCD w/ VGA input, 24V DC input
ID-H19ADC48	19" SunReadable front AI. LCD w/ VGA input, 48V DC input