


# PDU specification drawing

## 3-Phase 400V 32A monitored PDU : C13 x 48



32A model :	Fuse	MCB
VP48C13-32A-W/F_EN/2B-2	<b>6</b>	-
VP48C13-32A-W/CR_EN/2B-2	-	<b>6</b>

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
- Bank Details : **PH-1** < **Bank 1** > Output 16A max. C 13 # 1-15 (odd)  
< **Bank 2** > Output 16A max. C 13 # 2-16 (even)
- PH-2** < **Bank 3** > Output 16A max. C 13 # 1-15 (odd)  
< **Bank 4** > Output 16A max. C 13 # 2-16 (even)
- PH-3** < **Bank 5** > Output 16A max. C 13 # 1-15 (odd)  
< **Bank 6** > Output 16A max. C 13 # 2-16 (even)

**Three phase monitored PDU**  
Outlet : 10A Rated IEC320 C13 x 48

**Meter Features ( W monitored PDU )**

- Local Display : Field replaceable 2.8" color LCD with touchscreen
- Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor
- Accuracy : ±1% true RMS
- IP Access : via IP dongle, one IP Access up to 16 PDU Levels
- Cascade : Up to 16 PDU under single IP address via IP dongle
- SNMP : via IP dongle
- Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
- Safety Compliance : CE / LVD certified
- Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
- Storage Temperature : -25 to 65 °C
- Operating Altitude : 0 to 2,000 m
- Storage Altitude : 0 to 15,000 m
- Humidity : 8 to 95% RH, non-condensing

- Dimension : 78 (W) x 70 (D) x 1775 (H) mm
- Material : Steel
- Color : White ( outlet bracket )  
Black ( chassis )

