

LCD1U10-02 1U Rackmount LCD Keyboard/KVM Drawer



Options



BNC + S-Video



DVI-D



DC Power



Touch Screen



Audio


BNC + S-Video



DVI-D



DC Power



Touchscreen - USB



Touchscreen - Serial




Audio



****With touchscreen option, the height of 10-02 will be changed from 1U to 1.5U**

Diagram

Unit : mm



Dimensions

Model	Product Dimension (W x D x H)	Net Weight
LCD1U10-02	442 x 410 x 44 mm 17.4 x 16.1 x 1.73 inch	15 kg / 33 lbs

Drawer Features & Options

- 1U rackmount drawer with 10" LCD
- Combo interface either PS/2 or USB input to the LCD drawer
- Multiple keyboard language selections with either touchpad or trackball
- Slide rails with fixed positions to prevent drawer movement when typing
- Enhanced aesthetics with new molded front panel and two point lock

LCD Drawer & KVM Benefits

- ▶ Multi-user Matrix KVM with either 16 or 32 ports in 1U
- ▶ Cost efficient Combo KVM integration
- ▶ "One Man" installation slides for easy, quick installation
- ▶ Mix PS/2, USB & SUN with Multi-Platform switch capability
- ▶ Secure remote user access across the world wide web

Monitor

Grade A 10" industrial TFT LCD panel

- 10" 1024 x 768 LCD with 400 nit brightness and 1200:1 contrast ratio typical

Keyboard Selection

- N** Notebook KB w/ Touchpad **C** Cherry TM KB w/ Trackball

KVM Selection













Base Model

10" LCD Series















* Single port w/o KVM	LCD1U10-02
* Combo interface	










Matrix Cat6 KVM

	2 consoles	Matrix	Cat6	16 port	LCD1U10-02-MU162
	3 consoles				LCD1U10-02-MU163
	4 consoles				LCD1U10-02-MU164
IP 	3 consoles	Matrix IP	Cat6	16 port	LCD1U10-02-MU163IP
IP 	4 consoles				LCD1U10-02-MU164IP
IP IP 	4 consoles				LCD1U10-02-MU164IP2
	2 consoles	Matrix	Cat6	32 port	LCD1U10-02-MU322
	3 consoles				LCD1U10-02-MU323
	4 consoles				LCD1U10-02-MU324
IP 	3 consoles	Matrix IP	Cat6	32 port	LCD1U10-02-MU323IP
IP 	4 consoles				LCD1U10-02-MU324IP
IP IP 	4 consoles				LCD1U10-02-MU324IP2






Matrix DB-15 KVM

	2 consoles	Matrix	DB-15	8 port	LCD1U10-02-M82
	3 consoles				LCD1U10-02-M83
	4 consoles				LCD1U10-02-M84
IP 	3 consoles	Matrix IP	DB-15	8 port	LCD1U10-02-M83IP
IP 	4 consoles				LCD1U10-02-M84IP
IP IP 	4 consoles				LCD1U10-02-M84IP2
	2 consoles	Matrix	DB-15	16 port	LCD1U10-02-M162
	3 consoles				LCD1U10-02-M163
	4 consoles				LCD1U10-02-M164
IP 	3 consoles	Matrix IP	DB-15	16 port	LCD1U10-02-M163IP
IP 	4 consoles				LCD1U10-02-M164IP
IP IP 	4 consoles				LCD1U10-02-M164IP2


Combo Cat6 KVM

	1 console	Combo	Cat6	8 port	LCD1U10-02-U8KVM
	2 consoles				LCD1U10-02-U8KVM2
IP 	2 consoles				LCD1U10-02-U8KVM2IP
	1 console	Combo	Cat6	16 port	LCD1U10-02-U16KVM
	2 consoles				LCD1U10-02-U16KVM2
IP 	2 consoles				LCD1U10-02-U16KVM2IP
	1 console	Combo	Cat6	32 port	LCD1U10-02-U32KVM
	2 consoles				LCD1U10-02-U32KVM2
IP 	2 consoles				LCD1U10-02-U32KVM2IP

Combo DB-15 KVM

	1 console	Combo	DB-15	8 port	LCD1U10-02-8KVM-u
	2 consoles				LCD1U10-02-8KVM2
IP 	2 consoles				LCD1U10-02-8KVM2IP
	1 console	Combo	DB-15	16 port	LCD1U10-02-16KVM-u
	2 consoles				LCD1U10-02-16KVM2
IP 	2 consoles				LCD1U10-02-16KVM2IP

PS/2 DB-15 KVM

	1 console		8 port	LCD1U10-02-8KVM
			DB-15	16 port