


LCDR8U20-03 20.1" LCD RACK MOUNT MONITOR



- 20.1" TFT LCD display with 1600 x 1200 resolution.
- Steel construction with a durable powder coat finish.
- High contrast ratio for excellent picture quality.
- Optional Lexan™ screen protection.
- Mounts in 8U of rack space.
- Analog and Digital inputs.

Made in U.S.A.

GENERAL SPECIFICATIONS

Dimensions:

19.0" (W) x 14.0" (H) x 3.3" (D)

Weight:

18.0 lbs.

Power:

100 - 240 VAC, 50/60 Hz.
36 Watts max.

On-Screen Controls:

Brightness, Contrast, Horizontal & Vertical
Position, Auto Adjust, OSD H & V Position, Input Select
Color Temp., Reset.

Plug & Play:

DDC1 and DDC2B

Temperature:

Operating: 10°C to 40°C
Storage: -20°C to 45°C

Humidity:

Operating: 10 to 80% RH (max)

Input Signal (VGA):

R.G.B. analog video, TTL H & V sync.

Input Signal (Digital):

DVI-D (TMDS).

Input Connectors:

Analog: 15-pin mini D-Sub.
Digital: 24 pin DVI-D.

Colors Available:

Black.



DISPLAY SPECIFICATIONS

Display Type:

Active matrix TFT LCD

Display area:

20.1" Diagonal.

Colors Displayed:

16.7 million colors.

Contrast Ratio:

800:1

Brightness:

300 cd/m² typ.

Viewing Angle (CR>5):

Horizontal: 160°
Vertical: 160°

Response Time:

5 ms typ.

Resolution:

VGA up to 1600 x 1200.

Horizontal Frequency:

30 to 81 KHz.

Vertical Frequency:

56 to 75 Hz.

Specifications subject to change without notice.

Contact us about other options and our additional rack mount products.